




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
B		REVISED PER ECO-15-015252	13NOV15	BJ	FY
B1		REVISED PER ECO-16-003656	10MAR16	B.J	S.Y

D


C

B

A



- △ HOUSING MATERIAL: THERMOPLASTIC.
- △ CONTACT MATERIAL: COPPER ALLOY.
- △ FINISH:
 - MATING AREA: MEETS THE PERFORMANCE REQUIREMENTS OF PRODUCT SPECIFICATION 108-9063; BASED ON TELCORDIA DR-1217-CORE APPLICATIONS IN UNCONTROLLED ENVIRONMENTS.
- △ ACTION PIN POSTS REQUIRE 2.36 [.093] MIN THICK P.C. BOARD. RECOMMENDED P.C. BOARD HOLES ARE $\phi 1.151$ [.0453] PLATED THRU WITH 0.025-0.076 [.001-.003] COPPER, WITH 0.0076 [.0003] MIN TIN-LEAD PLATING; FINISHED HOLE AFTER PLATING $\phi 0.94-1.09$ [.037-.043].



SECTION Z-Z

				598051-1	
				PART NUMBER	
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. POLIGNONE	O4APROB	TE Connectivity	
		CHK A. SHARPE	O4APROB		
		APVD A. SHARPE	O4APROB		
		PRODUCT SPEC			
		APPLICATION SPEC			
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME ASSEMBLY, PIN, VERTICAL, HDI, 3 ROW, 96 POSITION, 18.62[.733] ACTION PIN POSTS WITH STABILIZERS	
		0 PLC ± -		SIZE A1	
		1 PLC ± -			
		2 PLC ± -			
		3 PLC ± 0.13 [.005]			
4 PLC ± -		APPLICATION SPEC		CAGE CODE 00779	
ANGLES ± ±		WEIGHT -			
MATERIAL 		FINISH 		DRAWING NO C=598051	
CUSTOMER DRAWING		SCALE 4:1		RESTRICTED TO -	
		SHEET 1 OF 1		REV B1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[598051-1](#)