




SUPERCEDED BY 66100-8 OBSOLETE	OBSOLETE	EUROPE			NONE	— 2 —66100— 2 —
	OBSOLETE				NONE	— 2 —66100— 1 —
		NORTH AMERICA	STANDARD		1-66101-9	2-66100-0
					1-66101-9	1-66100-9
					1-66101-4	— 1 —66100— 7 —
			—		—	— 1 —66100— 3 —
					66101-4	66100-9
					66101-3	66100-8
					66101-2	66100-7
					66101-1	66100-6
			STANDARD		66101-4	66100-4
			STANDARD		66101-3	66100-3
			STANDARD		66101-2	66100-2
			STANDARD		66101-1	66100-1
			TE ASSEMBLY LOCATION	REELING	BODY FINISH	LOOSE PIECE REF

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN V. FURLER 11JUL03 CHK G. STEINHAUER 11JUL03 APVD G. STEINHAUER 11JUL03		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME SOCKET ASSEMBLY, .062, TYPE III+ —	
		0 PLC ± — 1 PLC ± — 2 PLC ± 0.13 [.005] 3 PLC ± — 4 PLC ± — ANGLES ± —			
MATERIAL SEE CALLOUTS		FINISH SEE CALLOUTS			
		WEIGHT		SIZE A2	
				GAGE CODE 00779	
				DRAWING NO C-66100	
				RESTRICTED TO —	
CUSTOMER DRAWING				SCALE 8:1	
				SHEET 1 of 1	
				REV AM2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[66100-6](#)