


D

C

B

A



DIMENSION					PART- NO.			PART- NO.			PART- NO.		
					SELECTIVE GOLD PLATED			TIN PLATED			SELECTIVE GOLD PLATED		
A	B	C	F	-	1	5	7	WEIGHT POS. PER ROW			3	4	7
12.7	6.7	3.2	4.4	-	826629			826926					
12.0	6.7	2.5	4.4	-	826630			826935					
11.8	5.8	3.2	4.4	-	826646			826936			829070		
11.1	5.8	2.5	4.4	-	826647			826937					
14.0	8.0	3.2	4.4	-	826648			826938					
13.3	8.0	2.5	4.4	-	826649			826939					
12.7	6.7	3.2	5.5	-	-			-			828356		

CONTACT PIN	CuZn	SEE TABLE
PIN HOUSING	PBT GV	SEE TABLE
DESCRIPTION	MATERIAL	FABRE/COLOR/PLATING/SURFACE

NOTES:

- 1 MATING SIDE : AREA "F" MIN 0.7µm PdNi + MIN 0.1µm GOLD OVER 1.27µm NICKEL BY AREA "B"
SOLDER SIDE: MIN 3µm TIN OVER 1.27µm NICKEL
- 2 MATING AND SOLDER SIDE : MIN 3µm TIN OVER 1.27µm NICKEL
- 3 MATING SIDE: AREA "F" 0.13µm GOLD OVER 1.27µm NICKEL BY AREA "B"
SOLDER SIDE: MIN 3µm TIN OVER 1.27µm NICKEL
- 4 COLOR OF HOUSING: GREY
- 5 COLOR OF HOUSING: GREEN
- 6 TOLERANCES NOT CUMULATIVE
- 7 THE NUMBER OF POSITION PER ROW HAS TO BE ADDED TO THE BASE NO. AS A DASH NO.
EG: 2-826629-0 = 20 POSITIONS
- THE NUMBER OF POSITIONS PER ROW IS ALSO THE FACTOR FOR THE WEIGHT DETERMINATION
E.G: 20 X 0.0654 g = 1.308 g
- 8 OBSOLETE

SCALE 8:1
LAYOUT FOR HOLES ON PCB

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

±0.2mm

6

0 PLC ±

1 PLC ±

2 PLC ±

3 PLC ±

4 PLC ±

ANGLES ±

FINISH -

DWN G.HOLAUS 10NOV1989

CHK SCHAAERSCHMIDT M.

APVD

PRODUCT SPEC 108-18012

APPLICATION SPEC 114-25011

WEIGHT -

CUSTOMER DRAWING

TE Connectivity

NAME AMPMODU II PIN HEADER, SINGLE ROW, DUAL ROW, VERTICAL AND RIGHT ANGLE MOUNT

SIZE A2

CAGE CODE 00779

DRAWING NO C-826629

RESTRICTED TO -

SCALE 5:1

SHEET 1 OF 4

REV AC 1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2019

© COPYRIGHT 2019

BY- TE CONNECTIVITY

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			

POS. X 2.54 = L±0.5

(L-2.54)±0.1

2.54 ±0.1

2.8

2.54 ±0.1

5.0

F

B

A

0.3

C REF

0.63 ±0.05

"F" = GOLD AREA

(L-2.54)±0.1

2.54 ±0.1

2.54 ±0.1

1 ±0.05

SCALE 8:1

LAYOUT FOR HOLES ON PCB

DIMENSION					PART-NO.		PART- NO.			PART- NO.			
A	B	C	F	-	SELECTIVE GOLD PLATED			TIN PLATED	TIN PLATED	SELECTIVE GOLD PLATED			TIN PLATED
					1	5	7	2	5	7	3	4	7
12.7	6.7	3.2	5.5	-	826632			0.1276 g		826925		0.1279 g	
12.0	6.7	2.5	4.4	-	826633			0.1226 g		826941		0.1229 g	
11.8	5.8	3.2	4.4	-	826656			0.1212 g		826942		0.1217 g	
11.1	5.8	2.5	4.4	-	826657			0.1162 g		826943		0.1165 g	
14.0	8.0	3.2	4.4	-	826658			0.1366 g		826944		0.1370 g	
13.3	8.0	2.5	4.4	-	826659			0.1316 g		826945		0.1323 g	

CONTACT PIN	CuZn	SEE TABLE
PIN HOUSING	PBT GV	SEE TABLE
DESCRIPTION	MATERIAL	FABRE/COLOR/PLATING/SURFACE

NOTES:

1MATING SIDE : AREA "F" MIN 0.7µm PdNi + MIN 0.1µm GOLD OVER 1.27µm NICKEL BY AREA "B"
SOLDER SIDE: MIN 3µm TIN OVER 1.27µm NICKEL

2MATING AND SOLDER SIDE : MIN 3µm TIN OVER 1.27µm NICKEL

3MATING SIDE: AREA "F" 0.13µm GOLD OVER 1.27µm NICKEL BY AREA "B"
SOLDER SIDE: MIN 3µm TIN OVER 1.27µm NICKEL

4COLOR OF HOUSING: GREY

5COLOR OF HOUSING: GREEN

6TOLERANCES NOT CUMULATIVE

7THE NUMBER OF POSITION PER ROW HAS TO BE ADDED TO THE BASE NO. AS A DASH NO.
EG: 2-826632-0 = 20 POSITIONS

THE NUMBER OF POSITIONS PER ROW IS ALSO THE FACTOR FOR THE WEIGHT DETERMINATION
E.G: 20 X 0.1276 g = 2.552 g

8OBSOLETE

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN G.HOLAUS 10NOV1989

CHK SCHAAERSCHMIDT M.

APVD

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.2mm

0 PLC ±

1 PLC ±

2 PLC ±

3 PLC ±

4 PLC ±

ANGLES ±

FINISH -

MATERIAL SEE TABLE

-

PRODUCT SPEC 108-18012

APPLICATION SPEC 114-25011

WEIGHT -

CUSTOMER DRAWING

NAME AMPMODU II PIN HEADER, SINGLE ROW, DUAL ROW, VERTICAL AND RIGHT ANGLE MOUNT

SIZE A2

CAGE CODE 00779

DRAWING NO C-826629

RESTRICTED TO -

SCALE 5:1


SHEET 2 OF 4

REV AC1

1471-9 (3/13)

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			

D



“F” = GOLD AREA

DIMENSION						PART-NO.		PART- NO.		PART- NO.	
						SELECTIVE GOLD PLATED		TIN PLATED		SELECTIVE GOLD PLATED	
B	C	D	F	-			WEIGHT POS. PER ROW		WEIGHT POS. PER ROW		WEIGHT POS. PER ROW
6.7	3.2	1.3	4.4	-		826631	0.0757 g	826947/2	0.0760 g		
6.7	2.5	1.3	4.4	-		826651	0.0731 g	826948/2	0.0735 g		
5.8	3.2	1.3	4.4	-		826652	0.0726 g	826949/2	0.0728 g	829071	0.0726 g
5.8	2.5	1.3	4.4	-		826653	0.0701 g	826950/2	0.0704 g		
8.0	3.2	1.3	4.4	-		826654	0.0803 g	826951/2	0.0807 g		
8.0	2.5	1.3	4.4	-		826655	0.0777 g	826952/10	0.0782 g		
6.7	3.2	1.3	5.5	-		-	-	-	-	828419	0.0758 g


CONTACT PIN	CuZn	SEE TABLE
CONTACT PIN	CuSn6/9	SEE TABLE
PIN HOUSING	PBT GV	SEE TABLE
DESCRIPTION	MATERIAL	FABRE/COLOR/PLATING/SURFACE

NOTES:

- MATING SIDE : AREA “F” MIN $0.7 \mu\text{m}$ PdNi + MIN $0.1 \mu\text{m}$ GOLD OVER $1.27 \mu\text{m}$ NICKEL BY AREA “B”
SOLDER SIDE: MIN $3 \mu\text{m}$ TIN OVER $1.27 \mu\text{m}$ NICKEL
- MATING AND SOLDER SIDE : MIN $3 \mu\text{m}$ TIN OVER $1.27 \mu\text{m}$ NICKEL
- MATING SIDE: AREA “F” $0.13 \mu\text{m}$ GOLD OVER $1.27 \mu\text{m}$ NICKEL BY AREA “B”
SOLDER SIDE: MIN $3 \mu\text{m}$ TIN OVER $1.27 \mu\text{m}$ NICKEL
- COLOR OF HOUSING: GREY
- COLOR OF HOUSING: GREEN
- TOLERANCES NOT CUMULATIVE
- THE NUMBER OF POSITION PER ROW HAS TO BE ADDED TO THE BASE NO. AS A DASH NO.
EG: 2-826631-0 = 20 POSITIONS
- THE NUMBER OF POSITIONS PER ROW IS ALSO THE FACTOR FOR THE WEIGHT DETERMINATION
E.G: $20 \times 0.0757 \text{ g} = 1.514 \text{ g}$
- OBSOLETE
- MATING AND SOLDER SIDE : $2 \mu\text{m}$ TIN OVER $1.27 \mu\text{m}$ NICKEL

C

B



SCALE 8:1
LAYOUT FOR HOLES ON PCB

A

THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN G.HOLAUS CHK SCHAAERSCHMIDT M. APVD -		10NOV1989		 TE Connectivity			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: $\pm 0.2\text{mm}$ 		NAME		AMPMODU II PIN HEADER, SINGLE ROW, DUAL ROW, VERTICAL AND RIGHT ANGLE MOUNT				
		0 PLC 1 PLC 2 PLC 3 PLC 4 PLC ANGLES FINISH		PRODUCT SPEC 108-18012 APPLICATION SPEC 114-25011 WEIGHT -		SIZE A2		CAGE CODE 00779	DRAWING NO C=826629	RESTRICTED TO -
MATERIAL SEE TABLE -		-		CUSTOMER DRAWING		SCALE 5:1		SHEET 3 OF 4	REV AC 1	


D

C

B

A

D



"F" = GOLD AREA

DIMENSION						PART-NO.		PART- NO.		PART- NO.	
						SELECTIVE GOLD PLATED		TIN PLATED		SELECTIVE GOLD PLATED	
B	C	D	F	-		157	WEIGHT POS. PER ROW	257	WEIGHT POS. PER ROW	347	WEIGHT POS. PER ROW
6.7	3.2	1.3	4.4	-		826634	0.1646 g	826953	0.1656 g	8 828418	0.1651 g
6.7	2.5	1.3	4.4	-		8 826661	0.1597 g	8 826954	0.1606 g		
5.8	3.2	1.3	4.4	-		826662	0.1587 g	826955	0.1603 g	8 829072	0.1587 g
5.8	2.5	1.3	4.4	-		826663	0.1538 g	8 826956	0.1542 g		
8.0	3.2	1.3	4.4	-		826664	0.1741 g	826957	0.1749 g		
8.0	2.5	1.3	4.4	-		826665	0.1687 g	8 826958	0.1699 g		

CONTACT PIN	CuZn	SEE TABLE
PIN HOUSING	PBT GV	SEE TABLE
DESCRIPTION	MATERIAL	FABRE/COLOR/PLATING/SURFACE

NOTES:

- 1
- MATING SIDE : AREA "F" MIN 0.7µm PdNi + MIN 0.1µm GOLD OVER 1.27µm NICKEL BY AREA "B"
-
- SOLDER SIDE: MIN 3µm TIN OVER 1.27µm NICKEL

2

3

4


5

6

7

8

B



SCALE 8:1
LAYOUT FOR HOLES ON PCB

A

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

±0.2mm

6

0 PLC ±

1 PLC ±

2 PLC ±

3 PLC ±

4 PLC ±

ANGLES ±

FINISH -

MATERIAL

SEE TABLE

-

DWN

G.HOLAUS

10NOV1989

CHK

SCHAARSCHMIDT M.

APVD

-

PRODUCT SPEC

108-18012

APPLICATION SPEC

114-25011

WEIGHT

-

CUSTOMER DRAWING

TE Connectivity

NAME

AMPMODU II PIN HEADER, SINGLE ROW, DUAL ROW, VERTICAL AND RIGHT ANGLE MOUNT

SIZE

A2

CAGE CODE

00779

DRAWING NO

826629

RESTRICTED TO

-

SCALE

5:1

SHEET

4

OF

4

REV

AC1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[826629-4](#)