



## ANT-W63-FPC-UFL-100

### Flexible Embedded WiFi 6 Antenna

The Linx W63-FPC antenna is a flexible embedded multiband antenna offering excellent performance for WiFi 6E applications in the 6 GHz band (5.925 GHz to 7.125 GHz) plus 2.4 GHz and 5 GHz WiFi/WLAN for WiFi 5 and WiFi 6 solutions.

The ANT-LTE-WS-SMA antenna is made of rugged ABS plastic. The antenna's hinged, rotating, design allows for the antenna to be positioned for optimum performance and reduces the potential for damage from impact compared to a fixed whip design. The antenna attaches using an SMA plug (male pin) connector.

Connection is made to the radio via a 100 mm (3.94 in) long, 1.13 mm coaxial cable terminated in an MHF1/U.FL-compatible plug connector.

### FEATURES

- Performance at 5925 MHz to 7125 MHz
  - VSWR:  $\leq 2.6$
  - Peak Gain: 6.9 dBi
  - Efficiency: 67%
- Ground plane independent dipole antenna
- Compact, low-profile
  - 110 mm x 20 mm x 0.2 mm
- MHF1/U.FL-compatible plug (female socket) on 100 mm of 1.13 mm coaxial cable
- Adhesive backing permanently adheres to non-metal enclosures using 3M 467MP™/200MP adhesive
- Flexible to fit in challenging enclosures

### APPLICATIONS

- Complete WiFi/WLAN coverage
  - 802.11b/g
  - WiFi 4 (802.11n)
  - WiFi 5 (802.11ac)
  - WiFi 6 (802.11ax)
  - WiFi 6E (802.11ax)
- U-NII bands 1-4 and 5-8 (proposed)
- 2.4 GHz ISM applications
  - Bluetooth®
  - ZigBee®
- Internet of Things (IoT) devices
- Smart Home networking
- Sensing and remote monitoring

### ORDERING INFORMATION

Part Number	Description
ANT-W63-FPC-UFL-100	Antenna with 100 mm of 1.13 mm coaxial cable and MHF1/U.FL-compatible plug (female socket)

Available from Linx Technologies and select distributors and representatives.

## ELECTRICAL SPECIFICATIONS

ANT-W63-FPC-UFL-100	ISM/WiFi	U-NII 1-3	U-NII 5-8
Frequency Range	2400 MHz to 2485 MHz	5150 MHz to 5850 MHz	5925 MHz to 7125 MHz
VSWR (max.)	1.2	3.3	2.6
Peak Gain (dBi)	6.1	6.1	6.9
Average Gain (dBi)	-1.2	-1.5	-1.9
Efficiency (%)	80	74	69
Polarization	Linear		
Radiation	Omnidirectional		
Max Power	2 W		
Wavelength	1/2-wave		
Electrical Type	Dipole		
Impedance	50 $\Omega$		
Connection	MHF1/U.FL-compatible plug (female socket) on 100 mm (3.94 in) of 1.13 mm coaxial cable.		
Weight	1.5 g (0.05 oz)		
Dimensions	110.0 mm x 20.0 mm x 0.2 mm (4.33 in x 0.80 in x 0.01 in)		
Operating Temp. Range	-40 °C to +85 °C		

## PACKAGING INFORMATION

The ANT-W63-FPC-UFL-100 antennas are individually sealed in a clear plastic bag. Individual packages are packed in a bag of 100. Distribution channels may offer alternative packaging options.

## VSWR

Figure 1 provides the voltage standing wave ratio (VSWR) across the antenna bandwidth. VSWR describes the power reflected from the antenna back to the radio. A lower VSWR value indicates better antenna performance at a given frequency. Reflected power is also shown on the right-side vertical axis as a gauge of the percentage of transmitter power reflected back from the antenna.




Figure 1. W63-FPC Antenna VSWR with Frequency Band Highlights

## RETURN LOSS

Return loss (Figure 2), represents the loss in power at the antenna due to reflected signals. Like VSWR, a lower return loss value indicates better antenna performance at a given frequency.




Figure 2. W63-FPC Antenna Return Loss with Frequency Band Highlights

## PEAK GAIN

The peak gain across the antenna bandwidth is shown in Figure 3. Peak gain represents the maximum antenna input power concentration across 3-dimensional space, and therefore peak performance, at a given frequency, but does not consider any directionality in the gain pattern.




Figure 3. W63-FPC Antenna Peak Gain with Frequency Band Highlights

## AVERAGE GAIN

Average gain (Figure 4), is the average of all antenna gain in 3-dimensional space at each frequency, providing an indication of overall performance without expressing antenna directionality.




Figure 4. W63-FPC Antenna Average Gain with Frequency Band Highlights

## RADIATION EFFICIENCY

Return loss (Figure 5), represents the loss in power at the antenna due to reflected signals. Like VSWR, a lower return loss value indicates better antenna performance at a given frequency.






Figure 5. W63-FPC Antenna Radiation Efficiency with Frequency Band Highlights

## RADIATION PATTERNS


Radiation patterns provide information about the directionality and 3-dimensional gain performance of the antenna by plotting gain at specific frequencies in three orthogonal planes. Antenna radiation patterns (Figure 6), are shown using polar plots covering 360 degrees. The antenna graphic above the plots provides reference to the plane of the column of plots below it. Note: when viewed with typical PDF viewing software, zooming into radiation patterns is possible to reveal fine detail.



## 2400 MHz TO 2500 MHz (2450 MHz)



## 5150 MHz TO 5850 MHz (5500 MHz)



## 5850 MHz TO 7125 MHz (6500 MHz)




Figure 6. Radiation Patterns for ANT-W63-FPC-FPC-100 Antenna

## PRODUCT DIMENSIONS




Figure 7. ANT-W63-FPC-UFL-100 Dimensions

## ANTENNA MOUNTING

The ANT-W63-FPC-UFL-100 is a flexible, adhesive backed antenna that allows it to be permanently installed onto non-metallic surfaces. The adhesive backing is 3M 467MP™/200MP, which provides outstanding adhesion to high surface energy plastics. The adhesive delivers excellent shear strength to resist slippage and edge lifting, but can be repositioned temporarily to allow for repositioning. This adhesive is highly resistant to solvents, humidity and moisture, as well as heat up to 204 °C (400 °F) for short periods.

The antenna should never be bent to the point of creating a crease or allowing the angle of the bend to fall below 90 degrees (i.e. become acute) as this will impair function and may cause permanent damage.

---

## TE TECHNICAL SUPPORT CENTER

USA:	+1 (800) 522-6752
Canada:	+1 (905) 475-6222
Mexico:	+52 (0) 55-1106-0800
Latin/S. America:	+54 (0) 11-4733-2200
Germany:	+49 (0) 6251-133-1999
UK:	+44 (0) 800-267666
France:	+33 (0) 1-3420-8686
Netherlands:	+31 (0) 73-6246-999
China:	+86 (0) 400-820-6015

## te.com

TE Connectivity, TE, TE connectivity (logo), Linx and Linx Technologies are trademarks owned or licensed by the TE Connectivity Ltd. family of companies. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

TE Connectivity warrants to the original end user customer of its products that its products are free from defects in material and workmanship. Subject to conditions and limitations TE Connectivity will, at its option, either repair or replace any part of its products that prove defective because of improper workmanship or materials. This limited warranty is in force for the useful lifetime of the original end product into which the TE Connectivity product is installed. Useful lifetime of the original end product may vary but is not warrantied to exceed one (1) year from the original date of the end product purchase.

©2022 TE Connectivity. All Rights Reserved.

09/22    Original

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[ANT-W63-FPC-UFL-100](#)