


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
—	—		D	Contact pin base material change from CuSn (Phosphor bronze)to CuZn (Brass). Plating change from MIN. 0.8µm gold plating to min. 0.7µm Pd Ni + 0.1µm gold flash at contact area (Area F).	18JUL2014	TJ	JK

POLZ PRO REIHE	L±0.4	BESTELL-NR.	
-	-	-	-
2	5.08	-	-2
3	7.62	-	-3
4	10.16	-	-4
5	12.70	-	-5
6	15.24	-	-6
7	17.78	828 296	-7
8	20.32	-	-8
9	22.86	-	-9
10	25.40	1-	-0
11	27.94	1-	-1
12	30.48	1-	-2
13	33.02	1-	-3
14	35.56	1-	-4
15	38.10	1-	-5
16	40.64	1-	-6
17	43.18	1-	-7
18	45.72	1-	-8
19	48.26	1-	-9
20	50.80	2-	-0
21	53.34	2-	-1
22	55.88	2-	-2
23	58.42	2-	-3
24	60.96	2-	-4
25	63.50	2-	-5
26	66.04	2-	-6
27	68.58	2-	-7
28	71.12	2-	-8
29	73.66	2-	-9
30	76.20	3-	-0
31	78.74	3-	-1
32	81.28	3-	-2
33	83.82	3-	-3
34	86.36	3-	-4
35	88.90	3-	-5
36	91.44	3-	-6
37	93.98	3-	-7
38	96.52	3-	-8
39	99.06	3-	-9
40	101.60	4-	-0
41	104.14	4-	-1
42	106.68	4-	-2
43	109.22	4-	-3
44	111.76	4-	-4
45	114.30	4-	-5
46	116.84	4-	-6
47	119.38	4-	-7
48	121.92	4-	-8
49	124.46	4-	-9
50	127.00	5-	-0




STECKSEITE: IM BEREICH "F" 0.7µm PdNi+0.1µm GOLD FLASH
ÜBER 1.27µm NICKEL


LÖTSEITE: MIN. 2.5µm ZINN ÜBER 1.27µm NICKEL

OBSELETE PARTS: OBSELETE CIS STREAMLINING PER D.RENAUD/D.SINISI

1	CONTACT PIN	CuZn	2
COLOUR:GREEN	PIN HOUSING	PBT	1
FINISH/COLOR	PART DESCRIPTION	MATERIAL	ITEM NO.

OBSELETE 2

DIMENSIONS:		DWN	17.07.89		MATERIAL		SEE TABLE		FINISH		SEE TABLE			
mm		CHK	G.Holaus		TE Connectivity									
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	M.Schaarschmidt											
±0.2			—											
0 PLC	± —	PRODUCT SPEC			NAME									
1 PLC	± —	108—18012												
2 PLC	± —	APPLICATION SPEC			SPEZ. AMPMODU II STIFTLEISTE ZWEIREIHIG									
3 PLC	± —	—												
4 PLC	± —				SIZE	CAGE CODE	DRAWING NO			RESTRICTED TO				
ANGLES	± —	WEIGHT			A4	00779	C-828296			—				
		CUSTOMER DRAWING							SCALE	4:1	SHEET	1 of 1	REV	D



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[828296-3](#)