




Application Tooling > Applicators



Applicator Feed Type: **Pneumatic**

Applicator & Product Style: **Splice**

Crimp Type: **FFC Crimp**

Features

Contact Features

Crimp Type	FFC Crimp
------------	-----------

Other

Applicator Feed Type	Pneumatic
Applicator & Product Style	Splice

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability











Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts

 TE Part # 1719531-2 FFC,0,2,FOIL	 TE Part # 2455293-1 CONVERSION KIT 2 WIRES LEFT 2 RESISTORS	 TE Part # 965927-2 SPLICE F.DRAHT+FFC	 TE Part # 2455295-1 CONVERSION KIT WIRE RESISTOR WIRE RES
---	---	--	--

Customers Also Bought

 TE Part #7-1481301-1 WIRE CRIMPER TE	 TE Part #5-1481303-1 ANVIL - WIRE	 TE Part #5-1481303-2 KNIFE	 TE Part #8-1481301-1 FOIL CRIMPER
 TE Part #3-1481303-2 BASE PLATE, MATRICE	 TE Part #9-1481301-1 REFERENCE BLOCK	 TE Part #7-1481301-4 DOWN DEVICE	 TE Part #4-1481303-9 ANVIL - FOIL



Documents

Product Drawings

APPLICATOR, FFC F-CRIMP 6-8-POSITION

English

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2434675-2](#)