



Connectors > PCB Connectors > PCB Headers & Receptacles > PCB Mount Header: Wire-to-Board



PCB Connector Type: PCB Mount Header

PCB Mount Orientation: Right Angle

Connector System: Wire-to-Board

Number of Positions: 36

Number of Rows: 2

All PCB Mount Header: Wire-to-Board (16)

Features

Product Type Features

PCB Connector Type	PCB Mount Header
Connector System	Wire-to-Board
Header Type	Partially Shrouded
Sealable	No
Connector & Contact Terminates To	Wire & Cable
Connector Product Type	Connector Assembly

Configuration Features

PCB Mount Orientation	Right Angle
Number of Positions	36
Number of Rows	2

Body Features

Primary Product Color	Black
-----------------------	-------



Contact Features

Contact Underplating Material	Nickel
Contact Mating Area Plating Material	Tin (Sn)
Contact Type	Pin
Contact Current Rating (Max)	3 A

Termination Features

Termination Method to PCB	Surface Mount
---------------------------	---------------

Mechanical Attachment

PCB Mount Retention	With
PCB Mount Alignment	Without
Connector Mounting Type	Board Mount
Mating Alignment	With

Housing Features

Centerline (Pitch)	1.8 mm[.071 in]
--------------------	-----------------

Usage Conditions

Operating Temperature Range	-40 – 125 °C[-40 – 257 °F]
-----------------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Tape & Reel
------------------	-------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free



Solder Process Capability

Not reviewed for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 3-2834461-6  
MINI DYNAMIC REC HSG ASSY 36P X-KEY BLK


Also in the Series | Mini Dynamic Series




Connector Contacts(2)




PCB Headers & Receptacles(16)



Rectangular Power Connectors(1)



Wire-to-Board Connector Assemblies & Housings(15)



Wire-to-Board Headers & Receptacles (16)

Customers Also Bought



TE Part #6-2176329-1  
CRGP 1210 1M0 1%

TE Part #6-1879335-5  
CPF 0603 100R 1% 50PPM 1K RL

TE Part #2834464-6  
MD REC CONT TIN 22/24 AWG

TE Part #CAT-D9932-M6641A  
PCB Mount Header: Wire-to-Board

TE Part #CAT-D9932-M6641  
Receptacle Housing Assembly

TE Part #1630024-1  
HSC250 100R 5%

TE Part #2-2834627-4  
MD REC HSG ASSY 24P X-KEY BLK HF

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_3-2834465-6\_1.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_3-2834465-6\_1.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_3-2834465-6\_1.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[3-2834465-6](#)