






2377783-1 AS SHOWN



1.THIS TAB MATES WITH 2377780-X PLUG
(X=1, 2, 3, 4 FOR RELEVANT CODE).

2. MATERIAL:
SEE DRAWING TABLE





3. IDENTIFICATION FOR CABLE PINOUT.

4 DATE CODE: IDENTIFIES THE YEAR, MONTH, DAY AND HOUR OF ASSEMBLY.
YEAR: FIRST AND SECOND DIGITS(19=2019)
MONTH: THIRD DIGIT , EXCLUDING I , A=JAN, B=FEB, C=MARCH...(A=JANUARY)
DAY: FOURTH AND FIFTH DIGITS(13=13th DAY)
HOUR: SIXTH AND SEVENTH DIGITS(09=09AM)

5. PULL SECOND LOCK TO PRE-LOCK BEFORE TERMINAL INSERTION IN CASE OF SECOND LOCK BEING HIT TO END-LOCK POSITION.

6. REFER TO 114-18082 FOR TAB 1.6x0.6 TERMINAL APPLICATION SPECIFICATION.
APPLICABLE TERMINAL PART NUMBERS AND WIRE SIZE SHOWN AS BELOW FOR RECOMMEND,
CONSULT TE CONNECTIVITY FOR MORE APPLICATION INFORMATION.

1241846-1	TIN	1.5	Ø2.2~Ø2.4
964267-1	TIN	0.5-1.0	Ø1.4~Ø2.1
TERMINAL PN	TERMINAL PLATING	WIRE SIZE (MM2)	INSULATION WIRES ØD(MM)



																			
CODING A PN: 2377783-1					CODING B PN: 2377783-2					CODING C PN: 2377783-3					CODING D PN: 2377783-4				
(A1) (A1)	1	1	1	1	YELLOW	PA66-GF30	SECOND LOCK	2											
	1				BLUE	PA66-GF30	HOUSING.CODE D	1											
		1			GREEN	PA66-GF30	HOUSING.CODE C												
			1		PURPLE	PA66-GF30	HOUSING.CODE B												
				1	BROWN	PA66-GF30	HOUSING.CODE A												
	QTY. REQUEST PER ASSY				COLOR	MATERIAL	DESCRIPTION	ITEM NO											
	19.28	19.28	19.28	19.28	WEIGHT OF EACH ASSY NO. (g)														
A	A	A	A	REVISION OF EACH ASSY NO.															
2377783-4	2377783-3	2377783-2	2377783-1	TE ASSEMBLY PN															

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN V. TANG	31AUG2020		TE Connectivity			
		CHN F. JIANG	31AUG2020					
DIMENSIONS: mm 	TOLERANCES, UNLESS OTHERWISE SPECIFIED:		APVD LYN	31AUG2020		NAME 36POS. 1.6x0.6 TAB HSG. ASSY		
	0 PLC ±0.5		PRODUCT SPEC					
	1 PLC ±0.3		108-18957					
	2 PLC ±0.2		APPLICATION SPEC					
	3 PLC ±0.1		-		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
	4 PLC ±0.05		-		A2	00779	C=2377783	-
MATERIAL	FINISH		WEIGHT		CUSTOMER DRAWING			
-	-		-		SCALE	2:1	SHEET	1 OF 2
-	-				REV A1			

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			

APPLICATION AS SHOWN



NOTES:

- 7 .36POS.TAB AND PLUG HSG ASSY MATES WITH BULKHEAD BRACKET.
- 36POS. HSG ASSY P/N: MALE SIDE:2377783-*.FEMALE SIDE:2377780-*.
- BULKHEAD BRACKET P/N: 2050752-1 OR FOLLOW DIMENSIONS ON INTERFACE.
- IF THERE ARE ANY OTHER APPLICATIONS FOR THIS BRACKET, PLEASE CONFIRM WITH TE CONNECTIVITY FIRST.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN V. TANG 31AUG2020	TE Connectivity		
DIMENSIONS: mm		CHK E. JIANG 31AUG2020			
		APVD J. YIN 31AUG2020	NAME 36POS. 1.6x0.6 TAB HSG. ASSY		
		PRODUCT SPEC 108-18957	-		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC -	SIZE A2	CAGE CODE 00779	DRAWING NO C=2377783
MATERIAL -		WEIGHT -	RESTRICTED TO -		REV A1
CUSTOMER DRAWING		SCALE 2:1	SHEET 2	OF 2	REV A1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2377783-1](#)