


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AI	00		A	INITIAL REVISION	21AUG17	LS	GS

CRIMPAC II

FRONT VIEW

SIDE VIEW



Eigenschaften / Features

Ausgerichtet auf die industrielle Anwendung können unterschiedliche Querschnitte präzise verarbeitet werden.

Das Doppelführungssystem garantiert eine gleichmäßige Schließkraft und präzise verwindungssteife Führung in allen Profilen und ermöglicht so die Einhaltung kleinster Toleranzen.

These crimp tools are especially designed for industrial applications to precisely crimp cross-sections.

The double-guidance-system guarantees an even closing force and precise twist resistant guidance for every profile and thus ensures the compliance to the smallest tolerances.

Abmessungen / Dimension

Länge/Length: 220 mm

Breite/Width: 80 mm

Tiefe/depth: 25mm

Bedienungsanleitung /

Operating instructions



411-18629 / TE P/N 7-744017-6

THIS DRAWING IS UNPUBLISHED.

ALL INTERNATIONAL RIGHTS RESERVED.

BY TYCO ELECTRONICS CORPORATION.

© COPYRIGHT

DIMENSIONS:		DWN L. Sandhu	21AUG2017	MATERIAL		FINISH					
mm		CHK C. Witt	21AUG2017	 TE Connectivity							
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD G. Stegmayer	21AUG2017								
		PRODUCT SPEC						NAME CRIMPAC II, HT100, F- CRIMP			
0 PLC	± -	APPLICATION SPEC		-		RESTRICTED TO -					
1 PLC	± -			NAME							
2 PLC	± -	APPLICATION SPEC		-		RESTRICTED TO -					
3 PLC	± -			NAME							
4 PLC	± -	APPLICATION SPEC		-		RESTRICTED TO -					
ANGLES	± -			NAME							
		WEIGHT 0.52kg		SIZE A4		CAGE CODE 00779		DRAWING NO C-8-1579024-7		RESTRICTED TO -	
		CUSTOMER DRAWING		SCALE		SHEET 1 OF 1		REV A			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[8-1579024-7](#)