



RECOMMENDED PC BOARD LAY-OUT (SOLDERSIDE SHOWN)



EPOXY PC BOARDS WITH PLATED OR UNPLATED DRILLED HOLES

△ 1 EPOXY PC BOARD WITH UNPLATED DRILLED HOLES $1,00 \pm 0,05 \text{ mm}$.
FOR PLATED HOLES: SEE TABLE 1

△ EPOXY PC BOARDS WITH PLATED DRILLED HOLES, SOLDER EYE 1,40 MAX. TO ACHIEVE A CREEPAGE DISTANCE BETWEEN SOLDER EYE AND CONTACT AREA CONNECTOR OF MIN. 0,20mm.





PAPER PHENOLIC PC BOARDS WITH PUNCHED HOLES

 HOLE DIAMETER $0,80^{+0,15}_{-0}$

TABLE 1

P.C.B. HOLE DIM. PLATED			
FIN. HOLE	:0,95	TO	1,05 mm
Cu—thks	:0,025	TO	0,050 mm
Sn—thks	:0,004	TO	0,010 mm

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN P V TONGEREN 11-07-91 CHK H KOKKEN 11-07-91 APVD —		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± — 4 PLC ± — ANGLES ± —		NAME Micro MaTch FEMALE S.M.C. CONNECTOR —	
		PRODUCT SPEC 108-19052 APPLICATION SPEC 114-19027 WEIGHT —		SIZE A3	CAGE CODE 00779
MATERIAL —		FINISH —		DRAWING NO C-100411	
CUSTOMER DRAWING				SCALE 1:1	SHEET 2 OF 3
				REV G1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-100411-4](#)