



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
F 1		TYPO CORRECTIONS PER ECR-21-104935	14JUN2021	AFK	LS




SECTION A - A



Product Size	2.4	3.2	4.8	6.4	9.5	12.7	19.0	25.4	38.1
Minimum Sleeve Flattened Width	4.3 (.169)	6.5 (.256)	8.9 (.350)	11.0 (.433)	15.7 (.618)	20.7 (.815)	30.7 (1.209)	41.1 (1.618)	61.0 (2.402)
Nominal Sleeve Progression	12.70 (.500)	12.70 (.500)	12.70 (.500)	16.94 (.667)	25.40 (1.000)	29.64 (1.167)	42.34 (1.667)	50.80 (2.00)	72.0 (2.835)
"D" Minimum Supplied I.D.	2.40 (.094)	3.20 (.125)	4.80 (.189)	6.40 (.250)	9.50 (.375)	12.7 (.500)	19.0 (.750)	25.4 (1.00)	38.1 (1.50)
"d" Maximum Recovered I.D.	1.19 (.047)	1.60 (.063)	2.40 (.094)	3.20 (.126)	4.80 (.189)	6.40 (.250)	9.50 (.375)	12.7 (.500)	19.1 (.750)
"w" Recovered wall	0.50±0.10 (.020±.004)	0.50±0.10 (.020±.004)	0.51±0.11 (.020±.004)	0.65±0.15 (.026±.006)	0.65±0.15 (.026±.006)	0.65±0.15 (.026±.006)	0.75±0.15 (.030±.006)	0.90±0.15 (.035±.006)	1.00±0.20 (.039±.008)

DIMENSIONS IN mm (inches)



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		HX-SCE		RESTRICTED TO	
mm		OTHERWISE SPECIFIED:		PRODUCT SPEC		-		-	
0 PLC		± -		APVD		12FEB2020		SIZE	
1 PLC		± -		LS		RW-2072		CAGE CODE	
2 PLC		± -		APPLICATION SPEC		411-121008		DRAWING NO	
3 PLC		± -		WEIGHT		VARIOUS		SCALE	
4 PLC		± -		CUSTOMER DRAWING		A3		SHEET	
ANGLES		± -		N/A		0198G		1 OF 1	
FINISH		-		MATERIAL		CROSSLINKED POLYOLEFIN		REV	
								F1	



TE Connectivity

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[EM3184-000](#)