



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	00		H1	REVISED PER ECO-14-014232	19SEP2014	NK	MM



RECOMMENDED HOLE LAYOUT

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
H MOLL
23-10-87

CHK
T. CLARK
23-10-87

APVD
T. CLARK
29-10-87

PRODUCT SPEC

APPLICATION SPEC

WEIGHT -

CUSTOMER DRAWING

TE Connectivity

NAME
HEADER ASSY, MOD II, BREAKAWAY,
DOUBLE ROW, .100X.100 C/L, RIGHT
ANGLE, WITH .025 SQ POSTS

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=103326

RESTRICTED TO
-

SCALE
4:1

SHEET
1 OF 2

REV
H1

DIMENSIONS:
INCHES

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± .005

4 PLC ± -

ANGLES ± -

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

FINISH
SEE TABLE

MATERIAL
HOUSING:
FLAME RETARDANT
THERMOPLASTIC,
COLOR: BLACK
POSTS: COPPER ALLOY

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	- , - .
© COPYRIGHT - By -		ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			—	SEE SHEET 1	—	—	—

1 THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND HOUSING

 POINT OF MEASUREMENT FOR PLATING THICKNESS.

3 ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS

4 BREAKAWAY NOTCH ANGLE CAN BE ORIENTED TO THE RIGHT (AS SHOWN)
OR TO THE LEFT

5 .000015 GOLD IN THE CONTACT AREA, .000100-.000200 MATTE TIN-LEAD ON THE SOLDER TAIL, ALL OVER .000050 NICKEL

6 .000015 GOLD IN THE CONTACT AREA, .000100-.000200 MATTE TIN
ON THE SOLDER TAIL, ALL OVER .000050 NICKEL

 HIGH TEMPERATURE CONFIGURATION

8 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

7 7	6 6	3.984	3.900	39	80	9-103326-0	5 5	3.984	3.900	39	80	4-103326-0
7 7	6 6	3.884	3.800	38	78	8 8 8-103326-9	5 5	3.884	3.800	38	78	8 8 3-103326-9
7 7	6 6	3.784	3.700	37	76	8 8 8-103326-8	5 5	3.784	3.700	37	76	8 8 3-103326-8
7 7	6 6	3.684	3.600	36	74	8 8 8-103326-7	5 5	3.684	3.600	36	74	8 8 3-103326-7
7 7	6 6	3.584	3.500	35	72	8 8 8-103326-6	5 5	3.584	3.500	35	72	8 8 3-103326-6
7 7	6 6	3.484	3.400	34	70	8 8 8-103326-5	5 5	3.484	3.400	34	70	8 8 3-103326-5
7 7	6 6	3.384	3.300	33	68	8 8 8-103326-4	5 5	3.384	3.300	33	68	8 8 3-103326-4
7 7	6 6	3.284	3.200	32	66	8 8 8-103326-3	5 5	3.284	3.200	32	66	8 8 3-103326-3
7 7	6 6	3.184	3.100	31	64	8 8 8-103326-2	5 5	3.184	3.100	31	64	8 8 3-103326-2
7 7	6 6	3.084	3.000	30	62	8 8 8-103326-1	5 5	3.084	3.000	30	62	8 8 3-103326-1
7 7	6 6	2.984	2.900	29	60	8 8 8-103326-0	5 5	2.984	2.900	29	60	8 8 3-103326-0
7 7	6 6	2.884	2.800	28	58	8 7 7-103326-9	5 5	2.884	2.800	28	58	8 2 2-103326-9
7 7	6 6	2.784	2.700	27	56	8 7 7-103326-8	5 5	2.784	2.700	27	56	8 2 2-103326-8
7 7	6 6	2.684	2.600	26	54	8 7 7-103326-7	5 5	2.684	2.600	26	54	8 2 2-103326-7
7 7	6 6	2.584	2.500	25	52	8 7 7-103326-6	5 5	2.584	2.500	25	52	8 2 2-103326-6
7 7	6 6	2.484	2.400	24	50	8 7 7-103326-5	5 5	2.484	2.400	24	50	8 2 2-103326-5
7 7	6 6	2.384	2.300	23	48	8 7 7-103326-4	5 5	2.384	2.300	23	48	8 2 2-103326-4
7 7	6 6	2.284	2.200	22	46	8 7 7-103326-3	5 5	2.284	2.200	22	46	8 2 2-103326-3
7 7	6 6	2.184	2.100	21	44	8 7 7-103326-2	5 5	2.184	2.100	21	44	8 2 2-103326-2
7 7	6 6	2.084	2.000	20	42	8 7 7-103326-1	5 5	2.084	2.000	20	42	8 2 2-103326-1
7 7	6 6	1.984	1.900	19	40	8 7 7-103326-0	5 5	1.984	1.900	19	40	8 2 2-103326-0
7 7	6 6	1.884	1.800	18	38	8 6 6-103326-9	5 5	1.884	1.800	18	38	8 1 1-103326-9
7 7	6 6	1.784	1.700	17	36	8 6 6-103326-8	5 5	1.784	1.700	17	36	8 1 1-103326-8
7 7	6 6	1.684	1.600	16	34	8 6 6-103326-7	5 5	1.684	1.600	16	34	8 1 1-103326-7
7 7	6 6	1.584	1.500	15	32	8 6 6-103326-6	5 5	1.584	1.500	15	32	8 1 1-103326-6
7 7	6 6	1.484	1.400	14	30	8 6 6-103326-5	5 5	1.484	1.400	14	30	8 1 1-103326-5
7 7	6 6	1.384	1.300	13	28	8 6 6-103326-4	5 5	1.384	1.300	13	28	8 1 1-103326-4
7 7	6 6	1.284	1.200	12	26	8 6 6-103326-3	5 5	1.284	1.200	12	26	8 1 1-103326-3
7 7	6 6	1.184	1.100	11	24	8 6 6-103326-2	5 5	1.184	1.100	11	24	8 1 1-103326-2
7 7	6 6	1.084	1.000	10	22	8 6 6-103326-1	5 5	1.084	1.000	10	22	8 1 1-103326-1
7 7	6 6	.984	.900	9	20	8 6 6-103326-0	5 5	.984	.900	9	20	8 1 1-103326-0
7 7	6 6	.884	.800	8	18	8 5 5-103326-9	5 5	.884	.800	8	18	8 1 1-103326-9
7 7	6 6	.784	.700	7	16	8 5 5-103326-8	5 5	.784	.700	7	16	8 1 1-103326-8
7 7	6 6	.684	.600	6	14	8 5 5-103326-7	5 5	.684	.600	6	14	8 1 1-103326-7
7 7	6 6	.584	.500	5	12	8 5 5-103326-6	5 5	.584	.500	5	12	8 1 1-103326-6
7 7	6 6	.484	.400	4	10	8 5 5-103326-5	5 5	.484	.400	4	10	8 1 1-103326-5
7 7	6 6	.384	.300	3	8	8 5 5-103326-4	5 5	.384	.300	3	8	8 1 1-103326-4
7 7	6 6	.284	.200	2	6	8 5 5-103326-3	5 5	.284	.200	2	6	8 1 1-103326-3
7 7	6 6	.184	.100	1	4	8 5 5-103326-2	5 5	.184	.100	1	4	8 1 1-103326-2
7 7	6 6	.084			2	8 5 5-103326-1	5 5	.084			2	8 1 1-103326-1
REMARKS	PLATING	C	B	A	NO OF POSN	ASSEMBLY PART NUMBER	PLATING	C	B	A	NO OF POSN	ASSEMBLY PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 23-10-87 H MOLL CHK 23-10-87 T. CLARK APVD 29-10-87 T. CLARK		 TE Connectivity							
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME HEADER ASSY, MOD II, BREAKAWAY, DOUBLE ROW, .100X.100 C/L, RIGHT ANGLE, WITH .025 SQ POSTS							
		PRODUCT SPEC —									
		APPLICATION SPEC —									
MATERIAL		FINISH		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO				
SEE TABLE		WEIGHT —		A2	00779	C-103326	—				
CUSTOMER DRAWING						SCALE	1:1	SHEET	2 of 2	REV	H1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[6-103326-8](#)