



8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

7

OBSOLETE

7

OBSOLETE

7

OBSOLETE

<div><div></div><div>6</div></div>	<div><div></div><div>5</div></div>	64.01 [2.520]	65.91 [2.595]	24	25	7-103635-4
<div><div></div><div>6</div></div>	<div><div></div><div>5</div></div>	61.47 [2.420]	63.37 [2.495]	23	24	7-103635-3
<div><div></div><div>6</div></div>	<div><div></div><div>5</div></div>	58.93 [2.320]	60.83 [2.395]	22	23	<del>7-103635-2</del>
<div><div></div><div>6</div></div>	<div><div></div><div>5</div></div>	56.39 [2.220]	58.29 [2.295]	21	22	7-103635-1
<div><div></div><div>6</div></div>	<div><div></div><div>5</div></div>	53.85 [2.120]	55.75 [2.195]	20	21	<del>7-103635-0</del>
<div><div></div><div>6</div></div>	<div><div></div><div>5</div></div>	51.31 [2.020]	53.21 [2.095]	19	20	6-103635-9
<div><div></div><div>6</div></div>	<div><div></div><div>5</div></div>	48.77 [1.920]	50.67 [1.995]	18	19	<del>6-103635-8</del>
<div><div></div><div>6</div></div>	<div><div></div><div>5</div></div>	46.23 [1.820]	48.13 [1.895]	17	18	6-103635-7
<div><div></div><div>6</div></div>	<div><div></div><div>5</div></div>	43.69 [1.720]	45.59 [1.795]	16	17	6-103635-6
<div><div></div><div>6</div></div>	<div><div></div><div>5</div></div>	41.15 [1.620]	43.05 [1.695]	15	16	6-103635-5
<div><div></div><div>6</div></div>	<div><div></div><div>5</div></div>	38.61 [1.520]	40.51 [1.595]	14	15	6-103635-4
<div><div></div><div>6</div></div>	<div><div></div><div>5</div></div>	36.07 [1.420]	37.97 [1.495]	13	14	6-103635-3
<div><div></div><div>6</div></div>	<div><div></div><div>5</div></div>	33.53 [1.320]	35.43 [1.395]	12	13	6-103635-2
<div><div></div><div>6</div></div>	<div><div></div><div>5</div></div>	30.99 [1.220]	32.89 [1.295]	11	12	6-103635-1
<div><div></div><div>6</div></div>	<div><div></div><div>5</div></div>	28.45 [1.120]	30.35 [1.195]	10	11	6-103635-0
<div><div></div><div>6</div></div>	<div><div></div><div>5</div></div>	25.91 [1.020]	27.81 [1.095]	9	10	5-103635-9
<div><div></div><div>6</div></div>	<div><div></div><div>5</div></div>	23.37 [.920]	25.27 [.995]	8	9	5-103635-8
<div><div></div><div>6</div></div>	<div><div></div><div>5</div></div>	20.83 [.820]	22.73 [.895]	7	8	5-103635-7
<div><div></div><div>6</div></div>	<div><div></div><div>5</div></div>	18.29 [.720]	20.19 [.795]	6	7	5-103635-6
<div><div></div><div>6</div></div>	<div><div></div><div>5</div></div>	15.75 [.620]	17.65 [.695]	5	6	5-103635-5
<div><div></div><div>6</div></div>	<div><div></div><div>5</div></div>	13.21 [.520]	15.11 [.595]	4	5	5-103635-4
<div><div></div><div>6</div></div>	<div><div></div><div>5</div></div>	10.67 [.420]	12.57 [.495]	3	4	5-103635-3
<div><div></div><div>6</div></div>	<div><div></div><div>5</div></div>	8.13 [.320]	10.03 [.395]	2	3	5-103635-2
<div><div></div><div>6</div></div>	<div><div></div><div>5</div></div>	5.59 [.220]	7.49 [.295]	1	2	5-103635-1
REMARKS	PLATING	C	B	A	NO. OF POSN	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:  
mm [INCHES]

TOLERANCES UNLESS  
OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

MATERIAL

HOUSING  
FLAME RETARDANT  
CERAM BLACK  
CONTACTS BRASS

DWN  
S. SHUEY  
5-3-91

CHK  
L. CASTAGNA  
27-3-91

APVD  
L. CASTAGNA  
27-3-91

PRODUCT SPEC  
108-25034

APPLICATION SPEC  
114-25026

WEIGHT  
-

CUSTOMER DRAWING

TE Connectivity

NAME  
HDRASSY,RTANG,SGLEROW  
2.54[.100]C/L,0.64[.025]SOPST,  
WITHPLZN&LATCHING,AMPMODULE

SIZE  
A1

CAGE CODE  
00779

DRAWING NO  
103635

RESTRICTED TO  
-

SCALE  
1:1

SHEET  
2

OF  
2

REV  
T

4805 (1/15)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-103635-1](#)