




- ① CONTACTS ARE LATCHED INTO THE PRELOAD WINDOWS
- ② USE WITH #22-#26 AWG WIRE SIZE, .054/.030 INSULATION DIAMETER, .015 MAXIMUM INSULATION THICKNESS
- ③ THE DIMENSION APPLIES WITH THE FORWARD PRELOAD STOP IN CONTACT WITH THE HOUSING SURFACE
- ④ POINT OF MEASUREMENT FOR PLATING THICKNESS
- 5 FOR STRIP ASSEMBLIES SEE PART NUMBER 103946
- ⑥ MATERIAL- HOUSING: FLAME RETARDANT THERMOPLASTIC, COLOR: BLACK
PINS: PHOS. BRONZE
- ⑦ FINISH- PINS: .000030 GOLD IN THE CONTACT AREA,
.000050-.000100 BRIGHT TIN-LEAD ON THE TERMINATION AREA,
OVER .000050 NICKEL.
- ⑧ FINISH- PINS: .000030 GOLD IN THE CONTACT AREA,
.000050-.000100 MATTE TIN ON THE TERMINATION AREA,
OVER .000050 NICKEL.
- ⑨ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

8	2-103653-4	25	97-103893-4
8	2-103653-3	24	97-103893-3
8	2-103653-2	23	97-103893-2
8	2-103653-1	22	97-103893-1
8	2-103653-0	21	97-103893-0
8	1-103653-9	20	96-103893-9
8	1-103653-8	19	96-103893-8
8	1-103653-7	18	96-103893-7
8	1-103653-6	17	96-103893-6
8	1-103653-5	16	96-103893-5
8	1-103653-4	15	96-103893-4
8	1-103653-3	14	96-103893-3
8	1-103653-2	13	96-103893-2
7	2-103653-4	25	92-103893-4
7	2-103653-3	24	92-103893-3
7	2-103653-2	23	92-103893-2
7	2-103653-1	22	92-103893-1
7	2-103653-0	21	92-103893-0
7	1-103653-9	20	91-103893-9
7	1-103653-8	19	91-103893-8
7	1-103653-7	18	91-103893-7
7	1-103653-6	17	91-103893-6
7	1-103653-5	16	91-103893-5
7	1-103653-4	15	91-103893-4
7	1-103653-3	14	91-103893-3
7	1-103653-2	13	91-103893-2

SUPERSEDED BY 1-103946-1		1-103653-2	12	1-103893-1
SUPERSEDED BY 1-103946-0		1-103653-0	11	1-103893-0
SUPERSEDED BY 103946-9		103653-9	10	103893-9
SUPERSEDED BY 103946-8		103653-8	9	103893-8
SUPERSEDED BY 103946-7		103653-7	8	103893-7
SUPERSEDED BY 103946-6		103653-6	7	103893-6
SUPERSEDED BY 103946-5		103653-5	6	103893-5
SUPERSEDED BY 103946-4		103653-4	5	103893-4
SUPERSEDED BY 103946-3		103653-3	4	103893-3
SUPERSEDED BY 103946-2		103653-2	3	103893-2
SUPERSEDED BY 103946-1		103653-1	2	103893-1

PLATING	HOUSING PART NUMBER	NO OF POSN	ASSEMBLY PART NUMBER
---------	---------------------------	------------------	----------------------------

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. BROWN 26JUL00 CHK K. WRIGHT 26JUL00 APVD K. WRIGHT 26JUL00		 Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
DIMENSIONS: INCHES 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± .02 3 PLC ± .005 4 PLC ± - ANGLES ± - FINISH		NAME SHROUDED PIN ASSY, AMPMODU MTE, SINGLE ROW, .100 CL, POLARIZED, WITH LATCH WINDOWS, FOR #22-#26 AWG WIRE SIZE	
MATERIAL 		PRODUCT SPEC 108-25034 APPLICATION SPEC 114-25026 WEIGHT -		SIZE A2	CAGE CODE 00779
SEE TABLE		CUSTOMER DRAWING		DRAWING NO C-103893	RESTRICTED TO -
				SCALE 4:1	SHEET 1 OF 1
				REV M1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[6-103893-5](#)