




LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
AD	00		L	EC 0G3C 0675 04	08JAN04	BSV DFR
			L1	REVISED PER ECO-09-020932	27AUG09	KK AEG



- 1 .000050 MIN W.E. #1 GOLD ALLOY IN CONTACT AREA, .000050-.000100 TIN-LEAD IN AREA D, ALL OVER .000050 NICKEL.
- 2 MOLDED CIRCUIT #1 IDENTIFIER IN LOCATION SHOWN.
- 3 TOLERANCE NON-CUMALATIVE
- 4 USE WITH 22-26 AWG WIRE SIZE, .050 MAX INSULATION DIA., .015 MAX INSULATION WALL THICKNESS.
- 5 CONTACT IDENTIFICATION NUMBER "2" LOCATED IN THIS AREA.
- 6 .000050 MIN W.E. #1 GOLD ALLOY IN CONTACT AREA, .000050 - .000100 TIN IN AREA D, ALL OVER .000050 NICKEL.
- 7 ROHS 2002/95/EC COMPLIANT
- 8 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

8	OBSOLETE	7	6	.400	.300	3	8	5-104305-4
		7	6	1.000	.900	9	20	5-104305-3
		7	6	1.700	1.600	16	34	5-104305-2
		7	6	.500	.400	4	10	5-104305-1
		1		.400	.300	3	8	104305-4
		1		1.000	.900	9	20	104305-3
		1		1.700	1.600	16	34	104305-2
		1		.500	.400	4	10	104305-1
				C	B	A	NO OF POSN	ASSEMBLY PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN H MOLL 11-20-87		 Tyco Electronics Corporation Harrisburg, Pa 17105-3608					
		CHK P de Jong 11-20-87							
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME  RECEPTACLE ASSY, AMPMODU, MASS TERMINATION, DBL ROW, .100 X .100 CL, #22-#26 AWG WIRE					
		APVD —				PRODUCT SPEC  108-25018			
		—							
		APPLICATION SPEC							
		114-25015							
MATERIAL HOUSING: FLAME RETARDANT THERMOPLASTIC, COLOR:BLACK CONTACTS: PHOS BRONZE		FINISH SEE TABLE		SIZE A2	CAGE CODE 00779	DRAWING NO C=104305	RESTRICTED TO —		
				CUSTOMER DRAWING			SCALE 4:1	SHEET 1 of 1	REV L1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[104305-1](#)