



LOC	DIST	REVISIONS					
AJ	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			B	REV PER ECO 07-004710	3/2/2007	DW	KW



1052324-1
PART
NUMBER

ELECTRICAL	MECHANICAL	ENVIRONMENTAL
Nominal Impedance (Ω ms) 50	Interface Dimensions MIL-STD-348A, Fig. 310-1	TEMPERATURE RATING -65°C TO +165°C
Frequency Range (GHz) DC to 18	Recommended Mating Torque 7-10 IN-LBS	Vibration MIL-STD-202, Method 204, Condition D.
Volt Rating (VRMS MAX) @ Sea Level 335	Mating Characteristics:	Shock MIL-STD-202, Method 213, Condition B.
VSWR 1.05 +.005 f(GHz)	Insertion (MAX Lbs) N/A	Thermal Shock MIL-STD-202, Method 107, Condition B,
Insertion Loss (dB MAX) N/A $\sqrt{\quad}$	Withdrawal (MIN Ω z) N/A	Moisture Resistance MIL-STD-202, Method 106, Except Vibration
RF Leakage (dB MIN) -60 f(GHz)	Force to Engage and Disengage (In-Lbs MAX) 2.0	Shall Be Omitted.
Corona, 70,000 Ft (VRMS MIN) 250	Center Contact Captivation	Corrosion - MIL-STD-202, Method 101, Condition B, 5% salt spray
Dielectric Withstanding Voltage (VRMS MIN) @ Sea Level 1,000	Axial (Lbs) 6.0	
Contact Resistance (Milliohms MAX)	Radial (In- Ω z) 4.0	
Center Contact 3.0	Cable Retention	
Outer Contact 2.0	Axial Force (Lbs) N/A	
Cable to Housing N/A	Torque (In- Ω z) N/A	
RF High Potential @ Sea Level (VRMS MIN @ 5 MHz) 670	Weight (Grams) TBD	
I.R.(Megohms MIN) 10,000		

.XXX = in
XX.X = mm (REF)

HOUSING COUPLING NUT	STAINLESS STEEL PER ASTM-A484 AND ASTM-A582, TYPE 303	PASSIVATE PER QQ-P-35
DIELECTRIC	PTFE FLUOROCARBON PER ASTM-D-1457	N/A
CENTER CONTACT	BERYLLIUM COPPER PER ASTM-B-196 OR ASTM-B-197, ALLOY C17300, CONDITION H OR BRASS PER ASTM-B-16	GOLD PLATE PER MIL-G-45204
RETAINING RING	BERYLLIUM COPPER PER ASTM-B-194, ALLOY C17200, CONDITION H	N/A
GASKET	SILICONE RUBBER PER ZZ-R-765	N/A
COMPONENT	MATERIAL	FINISH

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RMK 5/14/69		tyco <i>Electronics</i> Tyco Electronics Corporation Harrisburg, PA 17105-3608			
		CHK BWC 5/15/69					
DIMENSIONS: INCHES		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		NAME			
		APVD DN 5/15/69		OSM STRAIGHT PANEL PLUG 4 HOLE FLANGE MOUNT RECEPTACLE SOLDER POT TERMINAL			
		PRODUCT SPEC —					
		APPLICATION SPEC —					
		—					
MATERIAL —		FINISH —		SIZE A2	CAGE CODE 00779	DRAWING NO C=1052324	RESTRICTED TO —
		CUSTOMER DRAWING		SCALE 5:1	SHEET 1 of 1	REV B	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2051-0000-02](#)