

			REVISIONS																																																							
			REV	DESCRIPTION	DATE	APPROVED																																																				
			04 ₁	REVISED	3/6/87	[Signature]																																																				
			B	PER EC 0U20-0694-00	10/2/01	C. Hoang																																																				
C	PER EC 0U20-0116-01	10/2/01	C. Hoang																																																							
<table><tr><td>ELECTRICAL</td><td>MECHANICAL</td><td>ENVIRONMENTAL</td></tr><tr><td>Nominal Impedance (Ohms) 50</td><td>Interface Dimensions</td><td>Temperature Rating -62°C to +85°C</td></tr><tr><td>Frequency Range (GHz) 2.0 to 12.0</td><td>OSN 304-1</td><td>Vibration MIL-STD-202, Method 204, Condition B</td></tr><tr><td>VSWR 1.2:1 MAX</td><td>OST 313-2</td><td>Shock MIL-STD-202, Method 213, Condition A</td></tr><tr><td>Insertion Loss (dB MAX) .35 dB MAX</td><td>Recommended Mating Torque 12-15 In-Lbs</td><td>Thermal Shock MIL-STD-202, Method 107, Condition I, Except High Temp 60°C</td></tr><tr><td>I.R.(Megohms MIN) 5,000</td><td>Mating Characteristics:</td><td>Moisture Resistance MIL-STD-202, Method 106 Shall Be Omitted</td></tr><tr><td rowspan="5">NOTES: 1. CAPTURED CENTER CONTACT</td><td>OSN OST</td><td>Corrosion - MIL-STD-202, Method B 101, Condition B, 5% salt spray</td></tr><tr><td>Insertion 2.0 2.0</td><td></td></tr><tr><td>Withdrawal 2.0 2.0</td><td></td></tr><tr><td>Force to Engage/Disengage OSN 6.0 In-Lbs OST 3.0 In-Lbs</td><td></td></tr><tr><td>Contact Retention</td><td></td></tr><tr><td>Axial (Lbs) N/A</td><td></td></tr><tr><td>Radial (In-Oz) N/A</td><td></td></tr><tr><td>Weight (Grams) TBD</td><td></td></tr></table>			ELECTRICAL	MECHANICAL	ENVIRONMENTAL	Nominal Impedance (Ohms) 50	Interface Dimensions	Temperature Rating -62°C to +85°C	Frequency Range (GHz) 2.0 to 12.0	OSN 304-1	Vibration MIL-STD-202, Method 204, Condition B	VSWR 1.2:1 MAX	OST 313-2	Shock MIL-STD-202, Method 213, Condition A	Insertion Loss (dB MAX) .35 dB MAX	Recommended Mating Torque 12-15 In-Lbs	Thermal Shock MIL-STD-202, Method 107, Condition I, Except High Temp 60°C	I.R.(Megohms MIN) 5,000	Mating Characteristics:	Moisture Resistance MIL-STD-202, Method 106 Shall Be Omitted	NOTES: 1. CAPTURED CENTER CONTACT	OSN OST	Corrosion - MIL-STD-202, Method B 101, Condition B, 5% salt spray	Insertion 2.0 2.0		Withdrawal 2.0 2.0		Force to Engage/Disengage OSN 6.0 In-Lbs OST 3.0 In-Lbs		Contact Retention		Axial (Lbs) N/A		Radial (In-Oz) N/A		Weight (Grams) TBD		<table><tr><td>HOUSING COUPLING NUT EXTRA HOUSING</td><td>STAINLESS STEEL PER ASTM-A484 AND ASTM-A582, TYPE 303</td><td>PASSIVATE PER QQ-P-35</td></tr><tr><td>DIELECTRIC</td><td>PTFE FLUOROCARBON PER ASTM-D-1457</td><td>N/A</td></tr><tr><td>CONTACT EXT.</td><td>BERYLLIUM COPPER PER ASTM-B-196 OR ASTM-B-197, ALLOY C17300, CONDITION H</td><td>GOLD PLATE PER MIL-G-45204</td></tr><tr><td>CENTER EXT. BUSHING & CENTER CONTACT</td><td>BRASS PER ASTM-B-16, HALF HARD</td><td>GOLD PLATE PER MIL-G-45204</td></tr><tr><td>RETAINING RING</td><td>BERYLLIUM COPPER PER ASTM-B-194, ALLOY C17200, CONDITION H</td><td>N/A</td></tr><tr><td>GASKET</td><td>SILICONE RUBBER PER ZZ-R-765</td><td>N/A</td></tr></table>			HOUSING COUPLING NUT EXTRA HOUSING	STAINLESS STEEL PER ASTM-A484 AND ASTM-A582, TYPE 303	PASSIVATE PER QQ-P-35	DIELECTRIC	PTFE FLUOROCARBON PER ASTM-D-1457	N/A	CONTACT EXT.	BERYLLIUM COPPER PER ASTM-B-196 OR ASTM-B-197, ALLOY C17300, CONDITION H	GOLD PLATE PER MIL-G-45204	CENTER EXT. BUSHING & CENTER CONTACT	BRASS PER ASTM-B-16, HALF HARD	GOLD PLATE PER MIL-G-45204	RETAINING RING	BERYLLIUM COPPER PER ASTM-B-194, ALLOY C17200, CONDITION H	N/A	GASKET	SILICONE RUBBER PER ZZ-R-765	N/A
			ELECTRICAL	MECHANICAL	ENVIRONMENTAL																																																					
			Nominal Impedance (Ohms) 50	Interface Dimensions	Temperature Rating -62°C to +85°C																																																					
			Frequency Range (GHz) 2.0 to 12.0	OSN 304-1	Vibration MIL-STD-202, Method 204, Condition B																																																					
VSWR 1.2:1 MAX	OST 313-2	Shock MIL-STD-202, Method 213, Condition A																																																								
Insertion Loss (dB MAX) .35 dB MAX	Recommended Mating Torque 12-15 In-Lbs	Thermal Shock MIL-STD-202, Method 107, Condition I, Except High Temp 60°C																																																								
I.R.(Megohms MIN) 5,000	Mating Characteristics:	Moisture Resistance MIL-STD-202, Method 106 Shall Be Omitted																																																								
NOTES: 1. CAPTURED CENTER CONTACT	OSN OST	Corrosion - MIL-STD-202, Method B 101, Condition B, 5% salt spray																																																								
	Insertion 2.0 2.0																																																									
	Withdrawal 2.0 2.0																																																									
	Force to Engage/Disengage OSN 6.0 In-Lbs OST 3.0 In-Lbs																																																									
	Contact Retention																																																									
Axial (Lbs) N/A																																																										
Radial (In-Oz) N/A																																																										
Weight (Grams) TBD																																																										
HOUSING COUPLING NUT EXTRA HOUSING	STAINLESS STEEL PER ASTM-A484 AND ASTM-A582, TYPE 303	PASSIVATE PER QQ-P-35																																																								
DIELECTRIC	PTFE FLUOROCARBON PER ASTM-D-1457	N/A																																																								
CONTACT EXT.	BERYLLIUM COPPER PER ASTM-B-196 OR ASTM-B-197, ALLOY C17300, CONDITION H	GOLD PLATE PER MIL-G-45204																																																								
CENTER EXT. BUSHING & CENTER CONTACT	BRASS PER ASTM-B-16, HALF HARD	GOLD PLATE PER MIL-G-45204																																																								
RETAINING RING	BERYLLIUM COPPER PER ASTM-B-194, ALLOY C17200, CONDITION H	N/A																																																								
GASKET	SILICONE RUBBER PER ZZ-R-765	N/A																																																								
<table><tr><td>COMPONENT</td><td>MATERIAL</td><td>FINISH</td></tr><tr><td>UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES</td><td>DRAWN BY SWA DATE 5/30/85</td><td rowspan="3">AMP Incorporated 140 Fourth Avenue Waltham, MA 02451-7599</td></tr><tr><td>FRAC. DEC. ANGLES</td><td>CHECKED BY FN 6/17/85</td></tr><tr><td>± 1/64 ±.005 ± 1°</td><td>APPD BY DRN 6/19/85</td></tr><tr><td rowspan="3">These drawings and specifications are the property of M/A COM Interconnect Div. and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of item(s) without written permission.</td><td>USE ASSY PROCEDURE</td><td>TITLE "OSN" PLUG TO "OST" JACK ADAPTER</td></tr><tr><td>NO. A.P. N/A</td><td>SIZE B CODE IDENT NO. 26805 3082-2310-00 REV 04₁</td></tr><tr><td></td><td>SCALE 3:1 SHEET 1 OF 1</td></tr></table>			COMPONENT	MATERIAL	FINISH	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES	DRAWN BY SWA DATE 5/30/85	AMP Incorporated 140 Fourth Avenue Waltham, MA 02451-7599	FRAC. DEC. ANGLES	CHECKED BY FN 6/17/85	± 1/64 ±.005 ± 1°	APPD BY DRN 6/19/85	These drawings and specifications are the property of M/A COM Interconnect Div. and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of item(s) without written permission.	USE ASSY PROCEDURE	TITLE "OSN" PLUG TO "OST" JACK ADAPTER	NO. A.P. N/A	SIZE B CODE IDENT NO. 26805 3082-2310-00 REV 04 ₁		SCALE 3:1 SHEET 1 OF 1																																							
COMPONENT	MATERIAL	FINISH																																																								
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES	DRAWN BY SWA DATE 5/30/85	AMP Incorporated 140 Fourth Avenue Waltham, MA 02451-7599																																																								
FRAC. DEC. ANGLES	CHECKED BY FN 6/17/85																																																									
± 1/64 ±.005 ± 1°	APPD BY DRN 6/19/85																																																									
These drawings and specifications are the property of M/A COM Interconnect Div. and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of item(s) without written permission.	USE ASSY PROCEDURE	TITLE "OSN" PLUG TO "OST" JACK ADAPTER																																																								
	NO. A.P. N/A	SIZE B CODE IDENT NO. 26805 3082-2310-00 REV 04 ₁																																																								
		SCALE 3:1 SHEET 1 OF 1																																																								

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[3082-2310-00](#)