





2

1

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			D	REVISED PER E.O. PI9510	18MAY2007	JA	RDR
			E	REVISED PER E.O. P20396	25JUN2010	JA	RDR
			F	REVISED PER ECO-15-007761	28MAY2015	RL	DM
			FI	REVISED PER PCN E-17-014802	06OCT2017	AJ	DM



SECTION A-A
WIRE BARREL



SECTION B-B
INSULATION BARREL




TE INTERNAL PN	DEUTSCH PN	PLATING
1060-16-0622	1060-16-0622	NICKEL
1060-16-0644	1060-16-0644	SELECTIVE GOLD
1060-16-0677	1060-16-0677	TIN
1060-16-0688	1060-16-0688	PALLADIUM NICKEL GOLD

3 MATERIAL: .012 [0.30] THICK COPPER ALLOY

2. WIRE RANGE: 20 AWG TO 16 AWG [0.5-1.0 mm²]
INSULATION RANGE: Ø.055-.100 [Ø1.40-2.54]

1 APPLIED ONLY TO SELECTIVE GOLD 1060-16-0644.
INDICATED DIMENSION SHOWS GOLD PLATED AREA.

NOTES: UNLESS OTHERWISE SPECIFIED

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN STEVE PALLUTH 28NOV2000		 TE Connectivity								
DIMENSIONS: INCHES[mm]		CHK VLADIMIR TOMSA 06DEC2000										
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD R. REED 08DEC2000		NAME STAMPED CONTACT PIN SIZE 16							
	0 PLC ±		PRODUCT SPEC									
	1 PLC ±		0425-015-0000									
		2 PLC ±		APPLICATION SPEC		SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO		
		3 PLC ±.025 [0.64]		114-151000		A3		4AFU8	Ⓒ-1060-16-06XX			
		4 PLC ±		WEIGHT 0.32 g								
MATERIAL 		FINISH SEE TABLE		Customer Drawing						SCALE 6:1	SHEET 1 OF 1	REV FI

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

TE Connectivity:

[1060-16-0688 \(Cut Strip\)](#) [1060-16-0622 \(Mouser Reel\)](#) [1060-16-0622 \(Cut Strip\)](#) [1060-16-0988 \(Mouser Reel\)](#) [1060-16-0644 \(Cut Strip\)](#) [1060-16-0644 \(Mouser Reel\)](#) [1060-16-0988 \(Cut Strip\)](#) [1060-16-0688 \(Mouser Reel\)](#) [1060-16-0644 \(Loose Piece\)](#) [1060-16-0622 \(Loose Piece\)](#) [1060-16-0688 \(Loose Piece\)](#) [1060-16-0988 \(Loose Piece\)](#)