



REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A1	REVISED PER ECO-11-005294	14APR11	HMR



CAPTURED CENTER CONTACT

ELECTRICAL	MECHANICAL	ENVIRONMENTAL
Nominal Impedance (Ohms) <u>50</u>	Force to Engage: (Lbs) <u>3.4 MAX</u>	Temperature Rating <u>-65°C to +165°C</u>
Frequency Range (GHz) <u>DC TO 6.0</u>	Force to Disengage: (Lbs) <u>1.77 MIN - 4.5 MAX</u>	Vibration <u>MIL-STD-202, Method 204,</u>
Voltage Rating (VRMS MAX) <u>335 @ Sea level</u>	Center Contact Captivation: <u>Axial 4.5lbs @ 1 minute</u>	<u>Condition B</u>
VSWR <u>N/A</u>	<u>with .006" displacement</u>	Thermal shock <u>MIL-STD-202, Method 107,</u>
Insertion Loss <u>N/A</u>		<u>Condition B</u>
Corona, 70,000 Ft (VRMS MIN) <u>250</u>		Moisture Resistance <u>MIL-STD-202, Method 106</u>
D.W.V. (VRMS MIN) <u>1000</u>		Corrosion <u>MIL-STD-202,</u>
Contact Resistance	<u>XX.XX = mm</u>	<u>Method 101, Condition B,</u>
Center Contact (Milliohms MAX) <u>5.0</u>	<u>.XXX = in</u>	<u>48 Hrs</u>
Outer Contact (Milliohms MAX) <u>1.0</u>		
RF High Potential (VRMS MIN @ 5 MHz) <u>670</u>		
I.R. (Megohms Min) <u>10,000</u>		

HOUSING

DIELECTRIC

CENTER CONTACT

BRASS, PER ASTM-B-16 HALF HARD

TFE FLUOROCARBON PER ASTM-D-1457

BERYLLIUM COPPER PER ASTM B 196, ALLOY C17300, CONDITION H

NICKEL PLATE PER QQ-N-290

N/A

GOLD PLATE PER MIL-G-45204

COMPONENT	MATERIAL	FINISH
<small>UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS TOLERANCE ON DEC ANGLES ±0.13 ± 1°</small>	<small>DRAWN BY DATE K.C.MAHER 10/18/90</small> <small>CHECKED BY M.Y. 10-19-90</small> <small>APPD BY QRL 10-19-90</small>	
<small>USE ASS'Y PROCEDURE</small> <small>N/A</small> <small>NO. AP _____</small>	<small>TITLE</small> OSX PRINTED WIRING BOARD JACK RECEPTACLE STRAIGHT TERMINAL	
	<small>SIZE</small> B	<small>CODE IDENT NO.</small> 26805
	<small>SCALE</small> 5 : 1	1060985-1
CUSTOMER DRAWING	<small>SHEET 1 OF 1</small>	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[060985](#)