

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20



COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

REVISIONS



P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	25FEB2015	GY	CW
	B	ECR-15-017607	03DEC 2015	GY	CW
	C	ECR-21-117384	05NOV2021	W QR	CW

NOTES:

1. TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC(Gray)
RATED VOLTAGE: CONDUCTOR-GROUND: 400V
CONDUCTOR-CONDUCTOR: 690V
RATED CURRENT: 35A
INSULATION RESISTANCE: >=400MΩ
RATED IMPULSE VOLTAGE: 6KV
POLLUTION DEGREE: 3
CONTACT RESISTANCE: <=5mΩ
FLAMMABILITY: UL94V-0
MATING CYCLES: 500
OPERATION TEMPERATURE: -40°C~+125°C
WIRE RANGE: 1.5mm²~6.0mm² (AWG16-AWG10)
CONTACT FINISH: SILVER PLATED
CONTACT TYPE: SCREW CLAMP (M4)



注释:

1. 技术参数:
绝缘材料: PC(Gray)
额定电压: 导体-地: 400V
导体-导体: 690V
额定电流: 35A
绝缘电阻: >=400MΩ
脉冲电压: 6KV
污染等级: 3
接触电阻: <=5 mΩ
阻燃等级: UL94V-0
插拔次数: 500
工作温度: -40°C~+125°C
接线范围: 1.5mm²~6.0mm² (AWG16-AWG10)
端子表面处理: 镀银
接线类型: 螺丝压接 (M4)





M4 thread, recommended tightening torque 1.2Nm

6 X M4 thread, recommended tightening torque 1.2Nm




4 X M3 thread, recommended tightening torque 0.5Nm



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



MATERIAL

-

-

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±
FINISH

-

-

DWN 10Dec2014

Gino.Yao

CHK 10Dec2014

Chris.Wang

APVD 10Dec2014

Xiang.Xu

PRODUCT SPEC

108-137052

APPLICATION SPEC

114-137052

WEIGHT

-

CUSTOMER DRAWING

HSB-006-M

T2060062101-000

DESCRIPTION

PART NUMBER



TE Connectivity

NAME

HSB-006-M

SIZE

A3

CAGE CODE

-

DRAWING NO

©T2060062101000

RESTRICTED TO

-

SCALE

1:1

SHEET

1 OF 1

REV

C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[T2060062101-000](#)