







PN 0-1, 0-3 & 0-5



PN 0-2,0-4 & 0-7




PN 0-6 & 0-8



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A8	REVISED PER ECR-16-016780	19SEP2017	NG	MKO

NOTES

- 1 Material: Housing: Aluminum diecasting alloy
seals: Neoprene
- 2 Surface:- Aluminium oxide + Varnish Black
-Grey
- 3 Varnish on the inside not necessary
- ⚠ Special- Logo
- 5 Packaging quantity 5 pieces in a box



OBSOLETE																
1										Hood HIP-K	Aluminium	Aluminium oxide	Blackl	8	Without Logo/thread	
	1									Hood HIP	Aluminium		Without varnish	7		
		1								Hood HIP-K	Aluminium	Aluminium oxide	Without varnish	6	Without M-Thread	
2	2	2	2	2	2	2	2	2		Pane	Stainless steel	Blank		5	B6.4	
2	2	2	2	2	2	2	2	2		Fixing screw	Stainless steel	Blank		4	M6x30	
1	1	1	1	1	1	1	1	1		Seal	Neoprene		Black	3		
						1	1			Hood HIP-K	Aluminium	Aluminium oxide	Black	2		
							1			Hood HIP	Aluminium		Grey	1		
0-8	0	7	0	6	0	5	0-4	0-2	0-3	0-1	DESCRIPTION	MATERIAL	SURFACE	COLOR	ITEM NO	REMARKS
										ORDERING TEXT						
										HIP.24/64.ST0.1.M40.G						
										HIP.24/64.ST0.1.M40.G						
										HIP.24/64.STS.1.M40.G						
										HIP-K.24/64.STS.1.M40.G						
										HIP-K.24/64.STS.1.M32.G						
										HIP-K.24/64.ST						
										HIP.24/64.STS.1.M40.G						

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN	Schneider	10.09.02	TE Connectivity			
				CHK	Schweiger	10.09.02				
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC		NAME		Hood		
mm		0 PLC ±		108-74030		HIP.24/64.1.M32/M4.0.G				
		2 PLC ±		APPLICATION SPEC		SIZE		CAGE CODE		
		3 PLC ±		116-74017		DRAWING NO		RESTRICTED TO		
		4 PLC ±		WEIGHT		A 1		00779		
		ANGLES		CUSTOMER DRAWING		SCALE		1:1		
		FINISH				SHEET		1 OF 1		
						REV		A8		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1106473-4](#)