







SUGGESTED MATING TAB



- 1
- MATL: #2 HARD BRASS OR NICKEL PLATE STEEL.
- 2
- NO BURRS PERMISSIBLE AT HOLE.
- 3
- TIN PLATING IS REQUIRED ON BRASS WHEN TERMINAL TEMPERATURE IS OVER 225°F
- 4
- MUST BE FLAT WITHIN 0.076 [0.003] OVER THIS LENGTH.
- 5
- HOLE MUST BE SYMMETRICAL ABOUT TAB ϕ WITHIN 0.076 [0.003].
- *
- TO BE USED ONLY WHEN SHOULDER IS ELIMINATED.



This specification lists various figures which indicate the direction a product comes off the top of the reel.



- 1
- CONTINUOUS STRIP ON REELS.
- 2
- ACCEPTS #22-#18 SINGLE WIRE SIZES, WIRE CRIMP IS 2.03 [0.080], F TYPE.
- 3
- FITS INSULATION RANGE 2.29-3.30 [0.090-0.130] DIA, INSULATION CRIMP IS 3.94 [0.155] F TYPE.

REELING
107-3 FIG.6

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± 0.25 [0.010]
3 PLC ± -
4 PLC ± -
ANGLES ± -
FINISH

MATERIAL
BRASS

SEE TABLE

DWN JR RUTH 6/26/98
CHK MS FEHER 6/26/98
APVD E HOWARD 6/26/98
PRODUCT SPEC
APPLICATION SPEC

WEIGHT 0

CUSTOMER DRAWING

OBSOLETE

TIN

1217097-2

-

-1217097-1-

FINISH

PART NO.

TE Connectivity

RECEPTACLE, POSITIVE-LOCK,
MARK III, 4.75 [0.187] SERIES

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A2

00779

1217097

1

1

REV

F1

SCALE

6:1

SHEET

1

REV

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1217097-1](#)