


1385598

1. RECOMMENDED SPARE PARTS.
2. GREASE LIGHTLY.
3. GUARD MUST BE IN PLACE WHEN OPERATING APPLICATOR IN A BENCH MACHINE.
4. LUBRICATE DAILY USING NO. 20 MACHINE OIL.
5. ITEMS WITH QTY OF REF SPECIFIED (EXCEPT ITEMS 78 AND 79) ARE USED ON ITEM 46.
6. 1800 CMA MAX ALLOWED.

QTY RECD PER ASSY			PARTS LIST		
DIMENSIONS IN INCHES. DO NOT SCALE PRINT.			MATL		HT TR
TOLERANCES UNLESS OTHERWISE SPECIFIED:			FIN		
2 PLG DEC ±			OR B.HIGMAN 210CT03 APP 210CT03 T.ELBIN		 Tyco Electronics Harrisburg, PA 17105-3608
4 PLG DEC ±			CHK REL		
ANGLES ±					
SURF TEXTURE: ✓			NAME SIDE FEED HDM APPLICATOR		MACHINE REF
REMOVE BURRS, BREAK SHARP EDGES R.015 MAX			SCALE DWG NO 1385598		MINI APPL
CASE CODE 00779			CUSTOMER AND ASSEMBLY DRAWING		
			RESTRICTED TO		

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1385598-3](#)