

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT

ALL RIGHTS RESERVED.

LOC

DIST



REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B1	ECR-16-009821	18JUL2016	GK	SD

REPLACED BY OCEAN STYLE APPLICATOR PART
NUMBER 2836073-1

FOR REPLACEMENT PARTS FOR APPLICATOR 1426104
REFER TO ADDITIONAL PAGE(S). SPARE PARTS KIT (IF LISTED)
WILL REMAIN AVAILABLE.

THE REPLACEMENT OCEAN STYLE APPLICATOR HAS THE
SAME TERMINATOR/PRESS INTERFACE AS APPLICATOR
1426104

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	GOPALAKRISHNA HV		 TE Connectivity	
		CHK	GOPALAKRISHNA HV			
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		
		0 PLC ±		APVD		
		1 PLC ±		STOUGH DALE		
		2 PLC ±		PRODUCT SPEC		
		3 PLC ±		APPLICATION SPEC		
4 PLC ±		4 PLC ±		SIZE		
ANGLES ±		FINISH		CAGE CODE		DRAWING NO
MATERIAL				A 3		©- 1426104
				WEIGHT		RESTRICTED TO
				CUSTOMER DRAWING		SCALE
				SHEET 1 OF 2		REV B1

AMP 1756 REV 3-92 24-III-03 15.27.20 us052641



QTY READ PER ASSY				PARTS LIST					
DIMENSIONS: mm [INCHES] DO NOT SCALE PRINT. TOLERANCES UNLESS OTHERWISE SPECIFIED: 1 PLC DEC +0.5 (.02 IN) 2 PLC DEC ± 3 PLC DEC ± ANGLES ± SURF TEXTURE: ✓				MATERIAL - -		HT TR - -		FIN - -	
				DR 01N0V00 APP 01N0V00 L.LOFTHOUSE F.BACKHURST		AMP AMP Incorporated Harrisburg, PA 17105-3608			
				CHK - REL -					
NAME SIDE FEED HD-I APPLICATOR				MACHINE REF HD-I APPL					
SCALE - <input checked="" type="checkbox"/> DWG NO 1426104				SHEET 1 OF 1		REV B			
REMOVE BURRS, BREAK SHARP EDGES R0.38 MAX									
CAGE CODE 00779				CUSTOMER AND ASSEMBLY DRAWING				RESTRICTED TO -	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1426104-2](#)