


									73
-	1	1	1	1	1	1	1426206	PRINT, APPLICATOR LOG SHEET	72
-	1	1	1	1	1	1	1338705-1	DOCUMENTATION PACKAGE	71
									70
									69
-	2	2	2	2	2	2	18025-1	WASHER, LOCK (M3) STR GDE	68
-	1	1	1	1	1	1	461264-1	PLATE, IDENTIFICATION	67
-	2	2	2	2	2	2	21017-2	SCR, DRIVE (#2x.19) ID PLATE	66
									65
-	1	1	1	1	1	1	986950-1	WASHER, FLAT PRECISION	64
-	1	1	1	1	1	1	3-18031-0	SCR, SKT SET (M6X6) RAM	63
-	1	1	1	1	1	1	SCR, 5HC (M4X6) INS DISC		62
-	2	2	2	2	2	2	1-18024-5	SCR, BHC (M5X25) DRAG	61
-	1	1	1	1	1	1	18024-7	SCR, BHC (M4X10) ANVIL	60
-	1	1	1	1	1	1	5-18022-2	SCR, HEX (M4X8) FEED FINGER	59

[illegible]

-	1	1	1	1	1	1	1633082-1	STRIP GUIDE PLATE ASSY	29
-	1	1	1	1	1	1	1-455888-5	SPACER, FRONT SHEAR DEP	28
-	2	2	2	2	2	2	1-22284-0	SPRING, DRAG	27
-	1	1	1	1	1	1	356835-1	LEVER, DRAG RELEASE	26
-	1	1	1	1	1	1	240792-1	DRAG, TERMINAL	25
-	1	1	1	1	1	1	1-690487-7	GUIDE, STRIP (FRONT)	24
-	1	1	1	1	1	1	980371-4	SCR,SHC SHLD	23
-	1	-	1	1	-	1	690472-6	STRIPPER	22
-	1	1	1	1	1	1	1-18023-1	SCR,SHC (M4X10) STRIPPER	21
-	4	4	4	4	4	4	18025-2	WASHER,LOCK (M4) STRIPPER	20
-	-	1	-	-	1	-	690472-5	STRIPPER	19
-	1	1	1	1	1	1	2-690518-9	HOLDER, TERMINAL	18
-	1	-	-	1	-	-	1338684-1	HOLDER, SHEAR, FRONT (NO-CUT)	17
-	2	2	2	2	2	2	18023-2	SCR,SHC (M3X6) REAR SHEAR PL	16
-	1	1	1	1	1	1	1-690691-1	PLATE, SHEAR (REAR)	15
-	-	1	1	-	1	1	1320920-1	HOLDER, SHEAR, REAR (CUT)	14
-	1	1	1	1	1	1	690463-1	SHEAR, FLOAT (REAR)	13
-	2	2	2	2	2	2	5-22280-0	SPRING, SHEAR	12
-	2	2	2	2	2	2	356885-4	STOP, SHEAR	11
-	-	1	1	-	1	1	1320921-1	HOLDER, SHEAR, FRONT (CUT)	10
-	1	1	1	1	1	1	462006-1	SHEAR, FLOAT (FRONT)	9
1	2	2	2	1	1	1	1-1333200-3	ANVIL	8
-	1	1	1	1	1	1	4-240641-6	SPACER, DEPRESSOR (REAR)	7
-	1	1	1	1	1	1	690468-2	DEPRESSOR, SHEAR (REAR)	6
-	1	1	1	1	1	1	1-455889-4	DEPRESSOR, SHEAR (FRONT)	5
-	1	1	1	1	1	1	238011-7	SPACER, BLOCK CRIMPER	4
1	2	2	2	1	1	1	8-456135-3	CRIMPER, INSULATION	3
-	1	1	1	1	1	1	455888-6	SPACER, CRIMPER	2
1	2	2	2	1	1	1	456401-3	CRIMPER, WIRE	1

						DIMENSIONS: mm [INCHES]		MATERIAL		HT TR		FIN	
						DO NOT SCALE PRINT.		TOLERANCES UNLESS OTHERWISE SPECIFIED:		DR M. CLIFFORD		29MAY01 APP F. BACHURST	
						1 PLC DEC ±0.5 [0.2 IN]		2 PLC DEC ±		REL 27JUN01		AMP AMP Incorporated Narberburg, PA 17105-3608	
						2 PLC DEC ±		3 PLC DEC ±		L. LOFTHOUSE			
						ANGLES:		NAME		SIDE FEED HD-I APPLICATOR		MACHINE REF	
						SURF TEXTURE:		SCALE		D DWO NO 1426206		HD-I APPL	
						REMOVE BURRS, BREAK SHARP EDGES R0.3R MAX						SHEET 1 OF 1	
												REV C	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1426206-6](#)