







THIS DRAWING IS UNPUBLISHED.
RELEASED FOR PUBLICATION
COPYRIGHT - By - TE CONNECTIVITY
ALL RIGHTS RESERVED.

LOC		DIST		REVISIONS				
HB	—	P	LTR	DESCRIPTION	DATE	DWN	APVD	
		E		REMOVED THE RIB ON THE BASE TO CASE ECO-15-011310	08-Dec-15	YS.H	HLC	
		E1		ADD NEW PN ECO-17-004477	17-Jan-18	WQ.Y	K.T	



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	H.Sasaki	TE Connectivity	
		CHK	Y.Oikawa		
		APVD	A.Nagai	NAME	
		PRODUCT SPEC		OJ-SH-LMH SPEC	
		APPLICATION SPEC			
		WEIGHT		SIZE	CAGE CODE
		CUSTOMER DRAWING		A3	00779
				DRAWING NO	1461247
				RESTRICTED TO	
				SCALE	5:1
				SHEET	1 of 2
				REV	E1

LOC	DIST	REVISIONS				
HB	-	P	LTR	DESCRIPTION	DATE	DWN
		-	-	SEE SHEET 1	-	-



NOTES:

1.LOT NO. SYSTEM AS FOLLOWING:

0 5 4 7
WEEK
YEAR

4.ADD LOT NO. SYSTEM AS FOLLOWING;

1 1 A
I II III

I, DIGITS FOR DAY OF THE WEEK

- 1...MONDAY IN THIS WEEK;
- 2...TUESDAY IN THIS WEEK;
-
- 7...SUNDAY IN THIS WEEK

II, DIGITS FOR SHIFT OF THE DAY

- 1...DAY SHIFT IN THIS DAY;
- 2...NIGHT SHIFT IN THIS DAY;

III, ONE CHARACTER DISTINGUISH THE LINE IDENTITY, SUCH AS: A,B,.....Z

2.TERMINAL DIMENSION IS BEFORE SOLDER DIP;

3.FOR THE TIN-PLATING OF THE PINS:

+0.1mm FOR WIDTH,THICKNESS AND DIAMETER.
+0.5mm FOR LENGTH.

FIG	PART NO	DESCRIPTION	PACKAGE SPEC.	PART B	PART A	TYPE
A	1461247-7	OJ-SH-112LMH	107-84030	12V	OJ-SH-112LMH	j
A	1461247-6	OJ-SH-105LMH	107-79010	5V	OJ-SH-105LMH	i
B	1461247-5	OJ-SH-112LMH	107-79010	12V	OJ-SH-112LMH	h
A	1461247-3	OJ-SH-124LMH	107-79010	24V	OJ-SH-124LMH	g
A	1419129-1	OJ-SH-118LMH	107-79010	18V	OJ-SH-118LMH	f
A	9-1419128-8	OJ-SH-112LMH	107-79010	12V	OJ-SH-112LMH	e
A	1461247-2	OJ-SH-109LMH	107-79010	9V	OJ-SH-109LMH	d
A	1461247-1	OJ-SH-106LMH	107-79010	6V	OJ-SH-106LMH	c
A	8-1419128-1	OJ-SH-105LMH	107-79010	5V	OJ-SH-105LMH	b
A	1461247-4	OJ-SH-103LMH	107-79010	3V	OJ-SH-103LMH	a

RELAY TYPE

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
0 PLC	± -
1 PLC	± -
2 PLC	± -
3 PLC	± -
4 PLC	± -
ANGLES	± -
MATERIAL	FINISH
-	-

DWN	H.Sasaki	-
CHK	Y.Oikawa	-
APVD	A.Nagai	-
PRODUCT SPEC	-	-
APPLICATION SPEC	-	-
WEIGHT	-	-
CUSTOMER DRAWING	-	-
SIZE	A3	00779
CAGE CODE	-	-
DRAWING NO	1461247	-
RESTRICTED TO	-	-
SCALE	5:1	-
SHEET	2 of 2	-
REV	E1	-

	UV RESIN	SEAL (VENT HOLE)	16
	EPOXY RESIN	SEAL (BASE & BOBBIN)	15
	JUEW	MAGNETIC WIRE	14
94V-0	P.B.T	CASE	13
94V-0	P.B.T	BASE	12
94V-0	P.B.T	BOBBIN	11
	SOLDER DIP	C.P WIRE	10
94V-0	P.P.S	CARD	9
	Ag ALLOY	MOVABLE CONTACT	8
	Ag ALLOY	NO.CONTACT	7
	STEEL	HINGE SPRING	6
	SOLDER DIP	Cu ALLOY	5
	SOLDER DIP	Cu ALLOY	4
	NIP	STEEL	3
	NIP	STEEL	2
	NIP	STEEL	1
INCOMBUSTIBILITY	TREATMENT	MATERIAL	DESCRIPTION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[8-1419128-1](#)