

LOC		DIST		REVISIONS					
HJ		-		P	LTR	DESCRIPTION	DATE	DWN	APVD
				B13		ECR-12-014500 (IMD obsolete)	18DEC2012	UKo	AK
				B14		ECR-12-021486 (Marking C to Q)	20DEC2012	UKo	JB
				C		ECR-13-014508	13JUN2013	UKo	Ak
				C1		ECR-14-007162 (Packaging information)	13OCT2015	AP	AK

Order Number - ABCCCC

Portugal made:

- A - Packing day
- B - Shift (1=day, 2=night)
- C - Lot number (sequential)

Other country made:

- A - Year (first digit)
- B - Year (second digit)
- C - Lot number (sequential)

H swiss made (until 2013)

PT Portugal made

Q China made

C China made (until 2012)

date code (YYWW)

Packaging data code (Box, bag, reels):
P(YWWDSL)000

Shipping data code:
YYWWDD

P - Product code (4 to IM relay)
Y(Y) - Year (last digit for packaging)
WW - calendar week (from date code)
D - Day of the week (1=Sat,.....and 7=Fri)
S - Shift (1=day shift, 2 night shift)
L - Production Line (line A, B, C)
000 - For internal use

Relay-Typ	Mark 1)	Mark 2)	PN (GR)	PN (JR)	PN (TS)	PN (KS/NS)
IM00..	00	1.5	3-1462037-7		3-1462037-5	
IM00NS	00N	1.5				
IM01..	01	3	1462037-1	4-1462037-0	1462037-4	
IM01B..	01B	3	4-1462039-5			
IM01C..	01C	3	1462038-4			
IM01NS	01N	3				1-1462038-1
IM01N..L	01N	3				4-1462039-3
IM02..	02	4.5	1462037-9	1-1462037-1	1-1462037-3	6-1462039-4
IM02..	02	4.5	8-1462039-1			
IM02..L	02	4.5	2-1462039-3			
IM02C..	02C	4.5	1462038-1			
IM02D..	02D	4.5	9-1462038-8			
IM02H..	02H	4.5	1-1462039-1			
IM02NS	02N	4.5				1-1462038-2

***obsolete**

DRAWING ALIAS: IM0C-DOK17

DIMENSIONS:		DWN	21FEB2003	MATERIAL	FINISH
mm		HD 9121		-	-
TOLERANCES UNLESS OTHERWISE SPECIFIED: DIN 7168-m		CHK HD 9121	21FEB2003	TE Connectivity	
		APVD HD 9121	21FEB2003		
		PRODUCT SPEC			
		APPLICATION SPEC			
0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±-		WEIGHT	-	NAME IM-Relay Marking	SIZE A4
		CUSTOMER DRAWING		CAGE CODE 00779	DRAWING NO C- 1462037-1
				RESTRICTED TO -	
				SCALE 10:1	SHEET 1 OF 6
				REV C1	

2000

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.

COPYRIGHT2000



[illegible]

2000 RELEASED FOR PUBLICATION	ALL RIGHTS RESERVED.	COPYRIGHT2000	THIS DRAWING IS UNPUBLISHED.		LOC	DIST	REVISIONS					
					HJ	-	P	LTR	DESCRIPTION	DATE	DWN	APVD
Relay-Typ	Mark 1)	Mark 2)	PN (GR)	PN (JR)	PN (TS)	PN (KS/NS)						
IM07C..	07C	24	1462039-2		1462039-1							
IM07D..	07D	24		7-1462039-4	7-1462039-2							
IM07NS	07N	24				1-1462038-7						
IM08I..	08I	2.4			1462047-3							
IM11..	11	3	9-1462038-5									
IM12..	12	4.5	1462039-3									
IM13..	13	5	1462039-4									
IM15..	15	9	8-1462039-5									
IM16..	16	12	1462039-5									
IM17..	17	24	1462039-6		4-1462039-6							
IM21..	21	3	2-1462039-6		1-1462039-5							
IM22..	22	4.5	2-1462039-7		2-1462039-8							
IM23..	23	5	2-1462039-9		3-1462039-0	6-1462039-7						
IM25..	25	9	3-1462039-5									
IM26..	26	12	3-1462039-1		3-1462039-2							
IM40..	40	1.5	5-1462037-1									
IM40D..	40D	1.5	8-1462039-4									
IM40NS	40N	1.5				1-1462038-8						
IM41..	41	3	5-1462037-4	5-1462037-5	5-1462037-3							
IM41C..	41C	3	4-1462039-2									
IM41D..	41D	3	6-1462039-8									
IM41NS	41N	3				1-1462038-9						
IM42..	42	4.5	3-1462037-1	5-1462037-7	5-1462037-6							
IM42C..	42C	4.5	4-1462039-1									
IM42D..	42D	4.5	1-1462039-9									
*obsolete												
DIMENSIONS:			DWN	21FEB2003	MATERIAL	DRAWING ALIAS:						
mm			HD 9121		-	IM0C-DOK17						
TOLERANCES UNLESS OTHERWISE SPECIFIED: DIN 7168-m			CHK	21FEB2003	TE Connectivity							
			HD 9121									
			APVD	21FEB2003								
			HD 9121									
0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±-			PRODUCT SPEC		NAME IM-Relay Marking							
			-									
			APPLICATION SPEC		SIZE A4							
			-									
			WEIGHT		CAGE CODE		DRAWING NO		RESTRICTED TO			
			-		00779		C- 1462037-1		-			
CUSTOMER DRAWING					SCALE	10:1	SHEET	3	OF	6	REV	C1


LOC HJ	DIST -	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			-	SEE SHEET 1	-	-	-

Relay-Typ	Mark 1)	Mark 2)	PN (GR)	PN (JR)	PN (TS)	PN (KS/NS)
IM42DNS	42D	4.5				1-1462039-6
IM42NS	42N	4.5				2-1462038-0
IM42P..	42P	4.5	5-1462039-7			
IM42PNS	42P	4.5				7-1462039-8
IM43..	43	5	5-1462037-9	6-1462037-0	5-1462037-8	
IM43C..	43C	5	9-1462038-7			
IM43NS	43N	5				2-1462038-1
IM44..	44	6	6-1462037-2	6-1462037-3	6-1462037-1	
IM44NS	44N	6				2-1462038-2
IM45..	45	9	6-1462037-4	6-1462037-5	3-1462037-2	
IM45I..	45I	9	1462047-5			
IM45NS	45	9				2-1462038-3
IM46..	46	12	6-1462037-7	6-1462037-8	6-1462037-6	
IM46C..	46C	12	8-1462039-0			
IM46NS	46N	12				2-1462038-4
IM46PNS	46P	12				6-1462039-1
IM47..	47	24	7-1462037-0		6-1462037-9	
IM47D..	47D	24		7-1462039-5		
IM47NS	47N	24				2-1462038-5
IM48..	48	2.4	1462039-8			
IM48D..	48D	2.4	1462039-9			
IM48I..	48I	2.4	1462047-1			
IM49I..	49I	2	1462047-4			

*obsolete

DRAWING ALIAS:

IM0C-DOK17


DIMENSIONS:		DWN HD 9121	21FEB2003		MATERIAL -		FINISH -							
mm		CHK HD 9121	21FEB2003		TE Connectivity									
TOLERANCES UNLESS OTHERWISE SPECIFIED: DIN 7168-m		APVD HD 9121	21FEB2003											
0 PLC	±-	PRODUCT SPEC -			NAME IM-Relay Marking									
1 PLC	±-													
2 PLC	±-	APPLICATION SPEC -			SIZE CAGE CODE DRAWING NO RESTRICTED TO									
3 PLC	±-													
4 PLC	±-	WEIGHT -			A400779C-1462037-1									
ANGLES	±-													
		CUSTOMER DRAWING					SCALE	10:1	SHEET	4	OF	6	REV	C1

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
HJ	-		-	SEE SHEET 1	-	-	-

Relay-Typ	Mark 1)	Mark 2)	PN (GR)	PN (JR)	PN (TS)	PN (KS/NS)
IM61..	61	3	7-1462039-7			
IM68..	68	2.4	8-1462039-2			
IMB01C..	B01C	3	1462041-1		1462041-4	
IMB02C..	B02C	4.5	1462041-2			
IMB03C..	B03C	5	1462041-7			
IMB03C..E	B03C	5	1-1462041-8			
IMB04C..	B04C	6	1462041-9		1-1462041-1	
IMB05C..	B05C	9	1-1462041-0		1-1462041-2	
IMB06C..	B06C	12	1462041-3		1462041-6	
IMB07C..	B07C	24	1-1462041-3		1-1462041-4	
IMB32B..	B32B	4.5	2-1462041-0			
IMB33B..	B33B	5	1-1462041-9			
IMB41C..	B41C	3	1-1462041-7			
IMB42C..	B42C	4.5	1-1462041-6		1-1462041-5	

*obsolete

DRAWING ALIAS: IM0C-DOK17

DIMENSIONS:		DWN HD 9121	21FEB2003	MATERIAL -		FINISH -							
mm		CHK HD 9121	21FEB2003	TE Connectivity									
TOLERANCES UNLESS OTHERWISE SPECIFIED: DIN 7168-m		APVD HD 9121	21FEB2003										
0 PLC	±-	PRODUCT SPEC		NAME IM-Relay Marking									
1 PLC	±-	-											
2 PLC	±-	APPLICATION SPEC		SIZE CAGE CODE DRAWING NO RESTRICTED TO									
3 PLC	±-	-											
4 PLC	±-	WEIGHT		A400779C-1462037-1									
ANGLES	±-	-											
		CUSTOMER DRAWING				SCALE	10:1	SHEET	5	OF	6	REV	C1

2000 RELEASED FOR PUBLICATION	ALL RIGHTS RESERVED.	COPYRIGHT2000	THIS DRAWING IS UNPUBLISHED.	©	*obsolete	LOC		DIST		REVISIONS					
						HJ	-	P	LTR	DESCRIPTION		DATE	DWN	APVD	
									-	SEE SHEET 1		-	-	-	
						Relay-Type	Mark 1)	Mark 2)	PN (GR)	PN (JR)	PN (TS)	PN (KS/NS)			
						IMC01..	C01	3	1462042-1		1462042-4				
						IMC02..	C02	4.5	1462042-2		1462042-5				
						IMC03..	C03	5	1462042-8		1462042-7				
IMC06..	C06	12	1462042-3		1462042-6										
IMC07..	C07	24	1-1462042-1		1-1462042-2										
IMC02C..	C02C	4.5	1-1462042-0												
IMC03C..	C03C	5	1-1462042-5												
IMC06C..	C06C	12	1462042-9		1-1462042-4										
IMC41C..	C41C	3			1-1462042-3										
IME01..	E01	3	1462043-1		1462043-5										
IME02..	E02	4.5	1462043-2		1462043-6										
IME03..	E03	5	1462043-3		1462043-7										
IME06..	E06	12	1462043-4		1462043-8										
IMF61..	F61	3	1462048-3												
IMF68..	F68	2.4	1-1462048-0												
DRAWING ALIAS: IM0C-DOK17															
DIMENSIONS:		DWN	21FEB2003	MATERIAL		FINISH									
mm		HD 9121		-		-									
TOLERANCES UNLESS OTHERWISE SPECIFIED: DIN 7168-m		CHK	21FEB2003	TE TE Connectivity											
		HD 9121													
		APVD	21FEB2003												
		HD 9121													
0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±-		PRODUCT SPEC		NAME IM-Relay Marking											
		-													
		APPLICATION SPEC		SIZE A4											
		-													
		WEIGHT		CAGE CODE		DRAWING NO		RESTRICTED TO							
		-		00779		C- 1462037-1									
CUSTOMER DRAWING		SCALE		10:1		SHEET		6 OF 6		REV C1					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[IM46TS](#)