






















































1. TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN THE HEADERS ARE HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD.
2. THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND THE HOUSING.
3. RETENTION FEATURES ON SOLDER TAILS, LOCATED AT MANUFACTURERS OPTION.
4.  FOR KINKED TAILS.
5. 0.00254-0.00504[.000100-.000200] MATTE TIN-LEAD,
ALL OVER 0.00127[.000050] NICKEL.
6. HOUSING: LCP, COLOR-BLACK.
POSTS: COPPER ALLOY.
7. 0.00254-0.00504[.000100-.000200] MATTE TIN,
ALL OVER 0.00127[.000050] NICKEL.
8. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

7	[101.19 3.984]	[99.06 3.900]	39	40	9-146290-0
7	[98.65 3.884]	[96.52 3.800]	38	39	8-146290-9
7	[96.11 3.784]	[93.98 3.700]	37	38	8-146290-8
7	[93.57 3.684]	[91.44 3.600]	36	37	8-146290-7
7	[91.03 3.584]	[88.90 3.500]	35	36	8-146290-6
7	[88.49 3.484]	[86.36 3.400]	34	35	8-146290-5
7	[85.95 3.384]	[83.82 3.300]	33	34	8-146290-4
7	[83.41 3.284]	[81.28 3.200]	32	33	8-146290-3
7	[80.87 3.184]	[78.74 3.100]	31	32	8-146290-2
7	[78.33 3.084]	[76.20 3.000]	30	31	8-146290-1
7	[75.79 2.984]	[73.66 2.900]	29	30	8-146290-0
7	[73.25 2.884]	[71.12 2.800]	28	29	7-146290-9
7	[70.71 2.784]	[68.58 2.700]	27	28	7-146290-8
7	[68.17 2.684]	[66.04 2.600]	26	27	7-146290-7
7	[65.63 2.584]	[63.5 2.500]	25	26	7-146290-6
7	[63.09 2.484]	[60.96 2.400]	24	25	7-146290-5
7	[60.55 2.384]	[58.42 2.300]	23	24	7-146290-4
7	[58.01 2.284]	[55.88 2.200]	22	23	7-146290-3
7	[55.47 2.184]	[53.34 2.100]	21	22	7-146290-2
7	[52.93 2.084]	[50.80 2.000]	20	21	7-146290-1
7	[50.39 1.984]	[48.26 1.900]	19	20	7-146290-0
7	[47.85 1.884]	[45.72 1.800]	18	19	6-146290-9
7	[45.31 1.784]	[43.18 1.700]	17	18	6-146290-8
7	[42.77 1.684]	[40.64 1.600]	16	17	6-146290-7
7	[40.23 1.584]	[38.10 1.500]	15	16	6-146290-6
7	[37.69 1.484]	[35.56 1.400]	14	15	6-146290-5
7	[35.15 1.384]	[33.02 1.300]	13	14	6-146290-4
7	[32.61 1.284]	[30.48 1.200]	12	13	6-146290-3
7	[30.07 1.184]	[27.94 1.100]	11	12	6-146290-2
7	[27.53 1.084]	[25.40 1.000]	10	11	6-146290-1
7	[24.99 0.984]	[22.86 0.900]	9	10	6-146290-0
7	[22.45 0.884]	[20.32 0.800]	8	9	5-146290-9
7	[19.91 0.784]	[17.78 0.700]	7	8	5-146290-8
7	[17.37 0.684]	[15.24 0.600]	6	7	5-146290-7
7	[14.83 0.584]	[12.70 0.500]	5	6	5-146290-6
7	[12.29 0.484]	[10.16 0.400]	4	5	5-146290-5
7	[9.75 0.384]	[7.62 0.300]	3	4	5-146290-4
7	[7.21 0.284]	[5.08 0.200]	2	3	5-146290-3
PLATING	C	B	A	NO. OF POSITIONS	PART NUMBER

NISI																																																																																																																								
------	--	---	---	---	---	---	---	---	---	---	---	---	---	---	---	--	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---	--

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T. HOFFMAN 12 JUN 95 CHK G. DUBNICNIK 02 JAN 96 APVD G. DUBNICNIK 02 JAN 96	 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0. F/LC ± 1. F/LC ± 0.51[.02] 2. F/LC ± 0.127[.005] 4. F/LC ± 0.0127[.0005] ANGLES ± FINISH SEE TABLE		
		NAME HEADER ASSEMBLY, MOD II, BREAKAWAY, SINGLE ROW, HIGH TEMPERATURE, VERTICAL WITH RETENTION FEATURE, W/.025 SQ. POSTS, 100CL		
MATERIAL		PRODUCT SPEC APPLICATION SPEC		
		SIZE CAGE CODE DRAWING NO. RESTRICTED TO A1 00779 C-146290		
WEIGHT —		CUSTOMER DRAWING		
		SCALE 4:1 SHEET 1 OF 1 REV K		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[9-146290-0](#)