





LOC		DIST		REVISIONS				
GP	00	P	LTR	DESCRIPTION	DATE	DWN	APVD	
			C	REV PER EC 09-028503	30DEC09	RG	DO	




SCALE 5:1

- 1 MATERIAL: BRASS
- 2 MATERIAL: HIGH CONDUCTIVITY COPPER ALLOY
- 3 FINISH: CONTACT MATING AREA .38μm MIN Au;
CRIMP AREA 2.03μm MIN. Sn;
UNDERPLATE OVERALL 1.27μm MIN. Ni
- 4 FINISH: CONTACT MATING AREA 1.27μm MIN Au;
CRIMP AREA 2.03μm MIN. Sn;
UNDERPLATE OVERALL 1.27μm MIN Ni
- 5 CONTACT SHOWN W/O CARRIER, OR HIDDEN LINES, FOR CLARITY
- 6 CUT OFF TO BE .13 MAX
- 7 INSULATION DIAMETER : 2.0-3.1 mm
- 8 WIRE DIAMETER: 16-20 AWG
- 10 THIS PRODUCT HAS NOT COMPLETED VALIDATION TESTING.
- 11 FINISH: ENTIRE CONTACT 1.27μm MIN Au;
UNDERPLATE OVERALL 1.27μm MIN Ni

























SCALE 12:1







SECTION A-A
SCALE 20:1



SECTION B-B
SCALE 20:1

			11.4	1-1489128-6
			9.8	1-1489128-5
			11.4	1-1489128-4
			9.8	1-1489128-3
	-		11.4	1-1489128-0
	-		9.8	1489128-9
	-		11.4	1489128-8
	-		9.8	1489128-7
	-		11.4	1489128-3
	-		9.8	1489128-2
MATERIAL	LOOSE PIECE	FINISH	DIM. "A"	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN CHK	AL FRANTUM -	15 MAY 02	 Tyco Electronics Corporation Middletown, Pa 17057	
DIMENSIONS: mm		APVD	-	NAME	MINI POWER DRAWER CRIMP PLUG CONTACT 16 - 20 GAUGE	
		PRODUCT SPEC 108-1998				
		APPLICATION SPEC 114-13067				
		SIZE CAGE CODE DRAWING NO				
		A1 00779 C=1489128				
		RESTRICTED TO				
MATERIAL	FINISH	WEIGHT	-	SCALE 4:1	SHEET 1 OF 1	REV C
				CUSTOMER DRAWING		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-1489128-3](#)