

Elektrische Werte

Bemessungsstrom	max. 25 A*
Durchgangswiderstand	< 3 mOhm

Werkstoff

Kontakt	Messing, vergoldet
Dichtung	FKM

Anschluss


Anschlussart/-bereich	Crimp/ 0,35 - 2,5 mm ²
- für Isolationscrimp	max. ø4,3 mm
Abisolierlänge	7 mm
Crimpeinstellungen	sind individuell zu wählen

Mechanische Werte

Steckzyklen	500
-------------	-----

Werkzeuge (nicht im Lieferumfang enthalten)

digitale Crimpzange	TE Teile Nr.: C0-0236-000-000 IC Ref. Nr.: C0.236.00
analoge Crimpzange	TE Teile Nr.: C0-0201-000-000 IC Ref. Nr.: C0.201.00
(Positioniereinsatz für 2 mm Kontakte	TE Teile Nr.: C0-0004-000-000 IC Ref. Nr.: C0.004.00)
Crimmmaschine	TE Teile Nr.: WA-1672-000-000 IC Ref. Nr.: WA10672
Digitaler Crimpeinsatz, mittel	TE Teile Nr.: C0-0373-000-000 IC Ref. Nr.: C0.373.00



Hauptabmessungen

Kontaktstift





intercontec
products

Contact Pin ø2 mm

for: - 940

TE part number: 61-0108-011-000
IC reference number : 61.108.11

Electrical Data

rated current max. 25 A*
contact resistance < 3 mOhm

Material

contacts brass, gold plated
seal FKM

Termination


cross-section crimp/ 0.35 - 2.5 mm²
- for insulation crimp max. ø4.3 mm
stripping length 7 mm
crimp settings select individually

Mechanical Data

mating cycles 500

Tools (not part of product contents)

digital crimping tool	TE part no.: C0-0236-000-000 IC ref. no.: C0.236.00
analog crimping tool	TE part no.: C0-0201-000-000 IC ref. no.: C0.201.00
(positioner for 2 mm contacts	TE part no.: C0-0004-000-000 IC ref. no.: C0.004.00)
crimping machine	TE part no.: WA-1672-000-000 IC ref. no.: WA10672
digital crimp insert, medium	TE part no.: C0-0373-000-000 IC ref. no.: C0.373.00



Main Dimensions

contact pin



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[61.108.11](#)