




8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

ALL RIGHTS RESERVED.

LOC

DIST

GP

00

REV

LYR

DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1

LED TARGET ZONE REF

4.25 REF

2.10

LED PLACED IN "Y" DIRECTION

1.35

LED PLACED IN "X" DIRECTION

G

G

PARTIAL BOTTOM VIEW

SCALE 12:1

10

LED HEIGHT OFF BOARD

1.23

LED PLACED IN "X" DIRECTION

2.10

LED PLACED IN "Y" DIRECTION

1.35

LED CENTER IN "X" OR "Y" DIRECTIONS

4.25

SECTION G-G

SCALE 12:1

10

	BLACK	9	0.00038 MIN	3.18	RETENTION BARB	3-1489841-9	12
	BLACK	9	0.00038 MIN	2.67	RETENTION BARB	3-1489841-8	12
	BLACK	8	0.00038 MIN	2.67	RETENTION BARB	3-1489841-7	12
SUPERCEDED BY 3-1489841-3	NATURAL	9	0.00000 MIN	4.00	RETENTION BARB	3-1489841-6	12
SUPERCEDED BY 3-1489841-2	NATURAL	9	0.00000 MIN	3.18	RETENTION BARB	3-1489841-5	12
SUPERCEDED BY 3-1489841-1	NATURAL	9	0.00008 MIN	2.67	RETENTION BARB	3-1489841-4	12
	NATURAL	9	0.00038 MIN	4.00	RETENTION BARB	3-1489841-3	12
	NATURAL	9	0.00038 MIN	3.18	RETENTION BARB	3-1489841-2	12
	NATURAL	9	0.00038 MIN	2.67	RETENTION BARB	3-1489841-1	12
	NATURAL	9	0.00076 MIN	4.00	RETENTION BARB	3-1489841-0	11
	NATURAL	9	0.00076 MIN	3.18	RETENTION BARB	2-1489841-9	11
	NATURAL	9	0.00076 MIN	2.67	RETENTION BARB	2-1489841-8	11
SUPERCEDED BY 2-1489841-4	NATURAL	9	0.00000 MIN	4.00	PLASTIC POST	2-1489841-7	12
SUPERCEDED BY 2-1489841-3	NATURAL	9	0.00000 MIN	3.18	PLASTIC POST	2-1489841-6	12
SUPERCEDED BY 2-1489841-2	NATURAL	9	0.00000 MIN	2.67	PLASTIC POST	2-1489841-5	12
	NATURAL	9	0.00038 MIN	4.00	PLASTIC POST	2-1489841-4	12
	NATURAL	9	0.00038 MIN	3.18	PLASTIC POST	2-1489841-3	12
	NATURAL	9	0.00038 MIN	2.67	PLASTIC POST	2-1489841-2	12
OBSOLETE	NATURAL	9	0.00076 MIN	4.00	PLASTIC POST	2-1489841-1	11
	NATURAL	9	0.00076 MIN	3.18	PLASTIC POST	2-1489841-0	11
	NATURAL	9	0.00076 MIN	2.67	PLASTIC POST	1-1489841-9	11
SUPERCEDED BY 3-1489841-3	NATURAL	8	0.00000 MIN	4.00	RETENTION BARB	1-1489841-8	12
SUPERCEDED BY 3-1489841-2	NATURAL	8	0.00000 MIN	3.18	RETENTION BARB	1-1489841-7	12
SUPERCEDED BY 3-1489841-1	NATURAL	8	0.00000 MIN	2.67	RETENTION BARB	1-1489841-6	12
SUPERCEDED BY 3-1489841-3	NATURAL	8	0.00030 MIN	4.00	RETENTION BARB	1-1489841-5	12
	NATURAL	8	0.00038 MIN	3.18	RETENTION BARB	1-1489841-4	12
	NATURAL	8	0.00038 MIN	2.67	RETENTION BARB	1-1489841-3	12
SUPERCEDED BY 3-1489841-0	NATURAL	8	0.00076 MIN	4.00	RETENTION BARB	1-1489841-2	11
	NATURAL	8	0.00076 MIN	3.18	RETENTION BARB	1-1489841-1	11
SUPERCEDED BY 2-1489841-8	NATURAL	8	0.00076 MIN	2.67	RETENTION BARB	1-1489841-0	11
SUPERCEDED BY 2-1489841-4	NATURAL	8	0.00000 MIN	4.00	PLASTIC POST	1489841-9	12
SUPERCEDED BY 2-1489841-3	NATURAL	8	0.00000 MIN	3.18	PLASTIC POST	1489841-8	12
SUPERCEDED BY 2-1489841-2	NATURAL	8	0.00000 MIN	2.67	PLASTIC POST	1489841-7	12
SUPERCEDED BY 2-1489841-4	NATURAL	8	0.00030 MIN	4.00	PLASTIC POST	1489841-6	12
SUPERCEDED BY 2-1489841-3	NATURAL	8	0.00038 MIN	3.18	PLASTIC POST	1489841-5	12
SUPERCEDED BY 2-1489841-2	NATURAL	8	0.00030 MIN	2.67	PLASTIC POST	1489841-4	12
SUPERCEDED BY 2-1489841-1	NATURAL	8	0.00076 MIN	4.00	PLASTIC POST	1489841-3	11
SUPERCEDED BY 2-1489841-0	NATURAL	8	0.00076 MIN	3.18	PLASTIC POST	1489841-2	11
SUPERCEDED BY 1-1489841-9	NATURAL	8	0.00076 MIN	2.67	PLASTIC POST	1489841-1	11
	EXTRACTOR COLOR	SOLDER TAIL	CONTACT GOLD INTERFACE	TAIL LENGTH	HOUSING STYLE	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED: 9 PLC ±0.5 1 PLC ±0.13 3 PLC ±0.013 4 PLC ±0.013 ANGLES FINISH

MATERIAL

DWN 04JAN2002

CHK M.CORRELL 04JAN2002

APVD M.CORRELL 20JUN2003

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

NAME

SIZE CAGE CODE DRAWING NO


RESTRICTED TO

SOCKET ASSEMBLY, DDR II SOLDER TAIL, 240 POSITION

A100779C-1489841

SCALE 4:1 SHEET 2 OF 3 REV B4

4805 (3/11)



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[3-1489841-0](#)