

									73
-	1	1	1	1	1	1	1528034	PRINT, APPLICATOR LOG SHEET	72
-	1	1	1	1	1	1	1338705-3	DOCUMENTATION PACKAGE	71
									70
									69
									68
-	1	1	1	1	1	1	461264-5	PLATE, IDENTIFICATION	67
-	2	2	2	2	2	2	21017-2	SCR,DRIVE (#2x.19) ID PLATE	66
									65
									64
-	1	1	1	1	1	1	3-18031-0	SCR,SKT SET (M6X6) RAM	63
									62
-	2	2	2	2	2	2	1-18024-5	SCR,BHC (M5X25) DRAG	61
-	1	1	1	1	1	1	18024-7	SCR,BHC (M4X10) ANVIL	60
-	1	1	1	1	1	1	5-18022-2	SCR,HEX (M4X8) FEED FINGER	59

[illegible][illegible]

									36
									35
-	1	1	1	1	1	1	1320934-5	SUPPORT, TERMINAL	34
-	2	2	2	2	2	2	1-18024-0	SCR,BHC (M4X20) STRIP GUIDE	33
-	1	1	1	1	1	1	18027-2	WASHER, FLAT (M4)	32
-	3	3	3	3	3	3	1-18023-2	SCR,SKT CAP (M4X12) MOUNT BLOCK	31


-	1	1	1	1	1	1	1320908-9	SPACER, STRIP GUIDE	30
-	1	1	1	1	1	1	1633073-1	STRIP GUIDE PLATE ASSY	29
-	1	1	1	1	1	1	1-455888-0	SPACER, FRONT SHEAR DEP	28
-	2	2	2	2	2	2	1-22284-0	SPRING, DRAG	27
-	1	1	1	1	1	1	356835-1	LEVER, DRAG RELEASE	26
-	1	1	1	1	1	1	240792-1	DRAG, TERMINAL	25
-	1	1	1	1	1	1	1320928-1	PLATE, STRIP GUIDE	24
-	1	1	1	1	1	1	980371-4	SCR,SHC SHLD	23
-	1	-	1	1	-	1	690472-2	STRIPPER	22
-	1	1	1	1	1	1	1-18023-1	SCR,SHC (M4X10) STRIPPER	21
-	4	4	4	4	4	4	18025-2	WASHER, LOCK (M4) STRIPPER	20
-	-	1	-	-	1	-	690472-1	STRIPPER	19

	-	-	-	-	-	1338684-1	HOLDER, SHEAR, FRONT (NO-CUT)	18
	-	1	-	-	1	-		17
								16
								15
								14
								13

[illegible]


									6
-	1	1	1	1	1	1	2-455889-0	DEPRESSOR, SHEAR (FRONT)	5
-	1	1	1	1	1	1	2-238011-5	SPACER, BLOCK CRIMPER	4
1	2	2	2	1	1	1	7-456135-8	CRIMPER, INSULATION	3
-	1	1	1	1	1	1	455888-3	SPACER, CRIMPER	2
1	2	2	2	1	1	1	3-456402-1	CRIMPER, WIRE	1

-77-76-72-71- - -2-1						PART NO		DESCRIPTION		ITEM NO	
						← REVISION OF EACH ASSY NO (WHEN BLANK, USE DWG REVISION)					
QTY REQD PER ASSY						PARTS LIST					
		DIMENSIONS: mm [INCHES]				MATL		HT TR		FIN	
		DO NOT SCALE PRINT.									
		TOLERANCES UNLESS OTHERWISE SPECIFIED:				DR 09JUL01		APP 09JUL01			
RK	JAN06	1 P/LC DEC ±0.5 [0.02 IN]				L.L.CLOTHOUSE		F. BACKHURST			
DS	6-02	2 P/LC DEC ±				CHK -		REL 09-08-01			
BH	FEB02	3 P/LC DEC ±						M.C.LIFFORD			
MC	FEB02	ANGLES ±				NAME		FINE ADJ SIDE FD HD-I APPL			
APP	AUG01	SURF TEXTURE: ✓				SCALE		D		MACHINE REF	
	DATE	REMOVE BURRS, BREAK SHARP EDGES R0.38 MAX				D		D		HD-I APPL	
						1528034				SHEET 1 of 1	
										REV D	



※ WARNING:
ON INSTALLATION, SET WIRE DISC TO LARGEST WIRE SIZE
SETTING. USE OF SETTINGS BELOW MIN REQ'D CRIMP
HEIGHT SETTING WILL CAUSE DAMAGE TO CRIMP TOOLING.

		D	ECR-06-001536	RK	JANU
		C	ECN 0150-0831-02	D5	6-02
		B	0150-0200-02	BH	FEB0
		A1	SEE ECN 015A-0080-02	MC	FEB0
		A	SEE ECN 015A-0642-01	MC	AUGO
P	F	LTR	REVISION RECORD	APP	DATE

DIMENSIONS: mm (INCHES)		MATL		HT TR		FIN	
DO NOT SCALE PRINT.		-		-		-	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		DR 09JUL01		APP 09JUL01			
1 PLC DEC ± 0.5 (.02 IN)		L. LOFTHOUSE		F. BACKHURST			
2 PLC DEC \pm		CHK -		REL 09-08-01		 AMP Amp Incorporated Harrisburg, PA 17105-3608	
3 PLC DEC \pm				M. CLIFFORD			
ANGLES -		NAME FINE ADJ SIDE FD HD-I APPL				MACHINE REF	
SURF TEXTURE: <input checked="" type="checkbox"/>						HD-I APPL	
REMOVE BURRS, BREAK SHARP EDGES RO.38 MAX		SCALE -		D		DWG NO	
				1528034		SHEET 1 of 1	
						REV D	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1528034-1](#)