

LOC —	DIST —	REVISIONS						
		P	LTR	DESCRIPTION	DATE	DWN	APVD	
			D9	REVISED PER ECO-12-012202	03JUL12	KH	MS	

5	2	104.7	112.2	—	—	10	4-1546307-7	
5	2	104.7	112.2	—	—	10	4-1546307-6	
5	4	104.7	112.2	—	—	10	4-1546307-5	
5	2	1	104.7	112.2	—	10	3-1546307-3	
		104.7	112.2	—	—	10	1-1546307-0	
5	3	2	1	95.2	102.7	—	9	5-1546307-0
5	3	2	1	95.2	102.7	4	9	4-1546307-9
3	2	1	95.2	102.7	4	9	9	4-1546307-8
		95.2	102.7	—	—	9		1546307-9
		85.7	93.2	—	—	8		1546307-8
		76.2	83.7	—	—	7		1546307-7
5	4	66.7	74.2	—	—	6		4-1546307-4
		66.7	74.2	—	—	6		1546307-6
5	2	57.2	64.7	—	—	5		4-1546307-3
5	2	57.2	64.7	—	—	5		4-1546307-2
5	2	57.2	64.7	—	—	5		4-1546307-1
5	2	57.2	64.7	—	—	5		4-1546307-0
5	4	57.2	64.7	—	—	5		3-1546307-9
		57.2	64.7	—	—	5		1546307-5
5	2	1	47.7	55.2	—	—	4	3-1546307-2
		47.7	55.2	—	—	4		1546307-4
5	2	38.2	45.7	—	—	3		3-1546307-8
5	2	38.2	45.7	—	—	3		3-1546307-7
5	2	38.2	45.7	—	—	3		3-1546307-6
5	2	38.2	45.7	—	—	3		3-1546307-5
5	4	38.2	45.7	—	—	3		3-1546307-4
		38.2	45.7	—	—	3		1546307-3
		28.7	36.2	—	—	2		1546307-2
		DIM B	DIM A	QC TAB .187 45° ②	QC TAB .187 FLAT ①	NO OF POSN	PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S SCHLEGEL 20AUG2002	STE TE Connectivity							
		CHK C RICHARD 8/20/02								
		APVD C RICHARD 8/20/02								
		PRODUCT SPEC								
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME 9.50MM (.374) DBL ROW BARRIER STRIP W/ WASHER						
		0 PLC ± — 1 PLC ± 0.3 2 PLC ± 0.25 3 PLC ± — 4 PLC ± — ANGLES ± 2°								
MATERIAL —		FINISH —		APPLICATION SPEC —		SIZE A3		CAGE CODE 00779	DRAWING NO C-1546307	RESTRICTED TO —
CUSTOMER DRAWING				SCALE 1:1		SHEET 1 OF 3		REV D9		

PHYSICAL PROPERTIES:
HOUSING MATERIAL: PBT
FLAMMABILITY: UL94V-0
COLOR: BLACK

TERMINAL:
TERMINALS: BRASS, TIN PLATED
SCREWS: 6-32, STEEL, NICKEL PLATED

MECHANICAL:
PITCH (TERMINAL SPACING): 9.50mm (.374")
WIRE RANGE: 12-22 AWG
RECOMMENDED TIGHTENING TORQUE: 12IN-LBS MAX.

ELECTRICAL PROPERTIES:
MAXIMUM CURRENT: 20A
OPERATING VOLTAGE: 300V

ENVIRONMENTAL PROPERTIES:
OPERATING TEMP RANGE: -40°C TO 120°C

- 1
- SCREWS ON ONE SIDE IN WIRE READY POSITION.

2


3

4


5

6


LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	APVD
—	—	—	—	SEE SHEET 1	—	—





3-1546307-1




3-1546307-2




3-1546307-3





3-1546307-7




3-1546307-8



3-1546307-6



3-1546307-5



294.7	302.2	—	—	30	3-1546307-0
285.2	292.7	—	—	29	2-1546307-9
275.7	283.2	—	—	28	2-1546307-8
266.2	273.7	—	—	27	2-1546307-7
256.7	264.2	—	—	26	2-1546307-6
247.2	254.7	—	—	25	2-1546307-5
237.7	245.2	—	—	24	2-1546307-4
228.2	235.7	—	—	23	2-1546307-3
218.7	226.2	—	—	22	2-1546307-2
209.2	216.7	—	—	21	2-1546307-1
199.7	207.2	—	—	20	3-1546307-1
199.7	207.2	—	—	20	2-1546307-0
190.2	197.7	—	—	19	1-1546307-9
180.7	188.2	—	—	18	1-1546307-8
171.2	178.7	—	—	17	1-1546307-7
161.7	169.2	—	—	16	1-1546307-6
152.2	159.7	—	—	15	1-1546307-5
142.7	150.2	—	—	14	1-1546307-4
133.2	140.7	—	—	13	1-1546307-3
123.7	131.2	—	—	12	1-1546307-2
114.2	121.7	—	—	11	1-1546307-1
DIM B	DIM A	QC TAB .187 45° ②	QC TAB .187 FLAT ①	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
—

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± —

1 PLC ± 0.3

2 PLC ± 0.25

3 PLC ± —

4 PLC ± —

ANGLES ± 2°

FINISH —

DWN S SCHLEGEL 20AUG2002

CHK C RICHARD 8/20/02

APVD C RICHARD 8/20/02

PRODUCT SPEC

APPLICATION SPEC

WEIGHT —

CUSTOMER DRAWING

TE Connectivity

NAME
9.50MM (.374) DBL ROW BARRIER STRIP
W/ WASHER

SIZE A3

CAGE CODE 00779

DRAWING NO C-1546307

RESTRICTED TO —

SCALE 1:1 SHEET 2 OF 3 REV D9

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[3-1546307-2](#)