

LOC		DIST		REVISIONS					
—		—		P	LTR	DESCRIPTION	DATE	DWN	APVD
				C1		P/N 1-829487-0 STATUS CORRECTED TO ACTIVE	28JUL2014	KJK	JK

POS.	L±0.4	PART NO.	
—	—	—	
2	5.08	—2	
3	7.62	—3	
4	10.16	—4	
5	12.70	—5	
6	15.24	—6	
7	17.78	829 487	—7
8	20.32	—8	
9	22.86	829 487	—9
10	25.40	1—	—0
11	27.94	1—	—1
12	30.48	1—	—2
13	33.02	1—	—3
14	35.56	1—	—4
15	38.10	1—	—5
16	40.64	1—	—6
17	43.18	1—	—7
18	45.72	1—	—8
19	48.26	1—	—9
20	50.80	2—	—0
21	53.34	2—	—1
22	55.88	2—	—2
23	58.42	2—	—3
24	60.96	2—	—4
25	63.50	2—	—5
26	66.04	2—	—6
27	68.58	2—	—7
28	71.12	2—	—8
29	73.66	2—	—9
30	76.20	3—	—0
31	78.74	3—	—1
32	81.28	3—	—2
33	83.82	3—	—3
34	86.36	3—	—4
35	88.90	3—	—5
36	91.44	3—	—6
37	93.98	3—	—7
38	96.52	3—	—8
39	99.06	3—	—9
40	101.60	4—	—0
41	104.14	4—	—1
42	106.68	4—	—2
43	109.22	4—	—3
44	111.76	4—	—4
45	114.30	4—	—5
46	116.84	4—	—6
47	119.38	4—	—7
48	121.92	4—	—8
49	124.46	4—	—9
50	127.00	5—	—0

CONTACT PIN	CuZn	△
HOUSING	PBT	GREEN
DESCRIPTION	MATERIAL	FINISH/COLOR

△ MATING SIDE: MIN 0.7µm PdNi+ MIN 0.1µm GOLD FLASH
IN ZONE "F" OVER 1.27µm NICKEL
SOLDER SIDE: 3.0 TO 5.0µm TIN OVER 1.27µm NICKEL.

DIMENSIONS:		DWN	21.09.90	MATERIAL	FINISH
mm		A.HO		—	—
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK	M.SCHAARSCHMIDT	TE Connectivity	
±0.2mm		APVD	—		
0 PLC ± —		PRODUCT SPEC		NAME AMPMODU II BREAK AWAY HEADER, SINGLE ROW	
1 PLC ± —		108-18012			
2 PLC ± —		APPLICATION SPEC		SIZE A4	
3 PLC ± —		—			
4 PLC ± —		WEIGHT		CAGE CODE 00779	
ANGLES ± —		—		DRAWING NO C-829487	
		CUSTOMER DRAWING		RESTRICTED TO —	
				SCALE 4:1	
				SHEET 1 OF 1	
				REV C1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[829487-7](#)