




## MULTIPLE CONFIGURATION PCB HEADERS & RECEPTACLES



✓ Active

TE CONNECTIVITY (TE)

### CONECTOR MODU 02P

AMPMODU | AMPMODU Headers

626249-2

TE Internal Number: 626249-2

Always EU RoHS/ELV Compliant

Applies To **Printed Circuit Board**

Connector Style **Plug**

Centerline **2.54 mm [ .1 in ]**

Number of Positions **2**

Header Type **Breakaway**

No documentation available.

Please review product documents or [contact us](#) for the latest agency approval information.

Product Type Features	Applies To	<b>Printed Circuit Board</b>
	Connector Style	<b>Plug</b>
	PCB Mounting Orientation	<b>Vertical</b>
	Connector Type	<b>Header</b>
	Row-to-Row Spacing	<b>2.54 mm [ .1 in ]</b>
	Strain Relief	<b>Without</b>
	Board Standoff	<b>With</b>
	Profile	<b>Standard</b>
	Product Type	<b>Connector</b>
	Sealed	<b>No</b>

Configuration Features	Number of Positions	<b>2</b>
	Number of Rows	<b>1</b>
	Staggered Rows	<b>No</b>
	Keyed	<b>No</b>
	Selectively Loaded	<b>No</b>

Body Features	Header Type	<b>Breakaway</b>
---------------	-------------	------------------

	Post Size	.64 mm [ .025 in ]
Contact Features	Contact Protection	Without
	Contact Shape	Square
	Underplate Material	Nickel
	Contact Type	Pin
	Contact Base Material	Brass
	Contact Mating Area Plating Thickness (µin)	30
	Solder Tail Contact Plating Material	Tin over Nickel
	Contact Mating Area Plating Material	Gold Flash, Gold
Termination Features	Termination Post Length	2.9 mm [ .114 in ]
	Termination End Plating Thickness	2.54 µm [ 100 µin ]
	Termination End Plating Material	Tin Over Nickel
	Termination Method to PC Board	Through Hole
	Contact Termination Type	Through Hole
Mechanical Attachment	PCB Mounting Style	Through Hole
	PCB Mount Retention	Without
	Panel Mount Retention	Without
	Mating Alignment	Without
	Mating Connector Lock	Without
Housing Features	Centerline	2.54 mm [ .1 in ]
	Housing Color	Black
	Housing Material	Thermoplastic
Dimensions	Mating Post Length	6.1 mm [ .24 in ]
Usage Conditions	High Temperature Housing	No
Operation/Application	High Speed Serial Data Connector	No
Packaging Features	Packaging Quantity	50
	Packaging Method	Box



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[626249-2](#)