






D


C

B

A




A-A



B-B

- △ MUST BE KEPT BETWEEN [X] AND 2
2. THE MATING PLUG HSG. PART NUMBER:
174516, 174515, 174514, 174913, 917992, 917989, 917981, 917975
3. RECOMMENDED MOUNTING SCREW; 3mm DIA, 6mm LENGTH (MAX.)
PAN HEAD, CLASS 2 TAPPING SCREW SPECIFIED IN JIS B1115, B1122
(TIGHTENING TORQUE; 4kg-cm MAX.)
4. APPLICABLE PRODUCT SPEC NO. : 108-5280, 108-5342
△ CIRCUIT NUMBER
POWER CIRCUIT NO. ① ~ ⑩
SIGNAL CIRCUIT NO. ⑪ ~ ⑮
△ INDICATED PREFIX AND ID MARK OF PRODUCT P/N BY COLOR HOT MARK
(APPLICABLE 0-174915-6 [0], 2-174915-7 [2])
(3-174915-6 [3], 4-174915-1 [4], 5-174915-7 [5])
- △ [X] 面から 2mm の範囲で測定
2. 嵌合相手 ハウジング型番 174516, 174515, 174514, 174913, 917992, 917989, 917981, 917975
3. 推奨取付ねじ: JIS B1115, B1122 タップピンねじ, 長さ 2mm
呼び径 3, 長さ 6mm 以下 (締付けトルク: 4kg-cm 以下)
4. 適用製品規格番号: 108-5280, 108-5342
△ 回路番号:
パワー回路 ① ~ ⑩
シグナル回路 ⑪ ~ ⑮
△ 適用製品型番のプリフィックス及び ID マークを
カラーホットマークにて表示
(適用製品型番 0-174915-6 [0], 2-174915-7 [2])
(3-174915-6 [3], 4-174915-1 [4], 5-174915-7 [5])



54	SELECTIVE-TIN [MATTE]	SELECTIVE GOLD × 9	—	13, 16, 69~75	NATURAL 自然色	4-5174915-1
56	SELECTIVE-TIN [MATTE]	PRE-TIN × 67 SELECTIVE GOLD × 3	12, 13, 14	—	GRAY 灰色	6-5174915-6
53	SELECTIVE-TIN [MATTE]	PRE-TIN × 73 SELECTIVE GOLD × 14	—	49~54, 61~68	GRAY 灰色	3-5174915-6
52	SELECTIVE-TIN [MATTE]	PRE-TIN × 62 SELECTIVE GOLD × 22	—	33~40, 49~54, 61~68	YELLOW 黄色	2-5174915-7
55	SELECTIVE-TIN [MATTE]	PRE-TIN × 54 SELECTIVE GOLD × 60	—	17~76	YELLOW 黄色	5-5174915-7
5	TIN-LEAD	PRE-TIN × 16 SELECTIVE GOLD × 60	—	17~76	YELLOW 黄色	5-174915-7
4	TIN-LEAD	PRE-TIN × 67 SELECTIVE GOLD × 9	—	13, 16, 69~75	NATURAL 自然色	4-174915-1
2	TIN-LEAD	PRE-TIN × 67 SELECTIVE GOLD × 22	—	33~40, 49~54, 61~68	YELLOW 黄色	2-174915-7
0	TIN-LEAD	PRE-TIN × 54 SELECTIVE GOLD × 60	—	17~76	GRAY 灰色	174915-6

MARKING マーキング	SOLDERING SIDE 半田付け面	CONTACT SIDE 接点側面	POWER CIRCUIT NO. パワー回路	SIGNAL CIRCUIT NO. シグナル回路	HOUSING COLOR ハウジング色	PART NUMBER 製品型番
△	CONTACT FINISH コネクタ仕上	△	GOLD PLATED CIRCUIT NO. 金めっき回路番号	△		

GENERAL TOLERANCE
D<≦ 10 : ±0.2
10<≦ 30 : ±0.25
30<≦ 100 : ±0.3
ANGLES : ±3°

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S.FUJITA CHK K.BETSUI	17NOV08	TE Connectivity	
DIMENSIONS: mm		APVD K.BETSUI	17NOV08	NAME 76POSITION CAP HOUSING ASSY 040/070 SERIES HYBRID I/O CONNECTOR	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		PRODUCT SPEC SEE TABLE		SIZE A1	
MATERIAL —		FINISH —		WEIGHT 37 g	
CUSTOMER DRAWING		SCALE 2:1		SHEET 1 of 1	
REV H6		DRAWING NO 00779		RESTRICTED TO —	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-174915-7](#)