





		1					
LOC	DIST	REVISIONS					
—	—	P	LTR	DESCRIPTION	DATE	DWN	APVD
			B	UPDATE PER ECO-08-031341	15 DEC 08	BJR	MKS

SIZE	A DIM	B DIM	C DIM	D DIM	E DIM ±.002	(L DIM)
05	.470	.233	.310	.620	.315	(.100)
09	.570	.333	.410	.720	.415	(.200)
15	.720	.483	.560	.870	.565	(.350)
25	.970	.733	.810	1.120	.815	(.600)
37	1.270	1.033	1.110	1.420	1.115	(.900)
51	1.620	1.383	1.460	1.770	1.465	(1.250)



- 1

SHELL OPTIONS (TO BE SPECIFIED IN NANONICS PART NUMBER):
6061-T6 ALUMINUM, ELECTROLESS NICKEL PLATED PER SAE-AMS-C-26074 (STANDARD) OR GOLD PLATED PER ASTM B488;
OR 303 STAINLESS STEEL, PASSIVATED PER SAE-AMS-2700
INSULATOR MATERIAL IS LIQUID CRYSTAL POLYMER (LCP) PER MIL-M-24519 OR PER ASTM D5138
- 2

STANDARD 1.0 X 0.25mm JACKSCREW THREADS ARE SHOWN FOR REFERENCE ONLY AND MUST BE SPECIFIED IN THE
NANONICS PART NUMBER WHEN REQUIRED. 1.2 X 0.25mm THREADS ALSO AVAILABLE.
- 3

THIS CONFIGURATION MAY BE TERMINATED WITH 28 AWG SOLID, 30 AWG STRANDED OR SMALLER WIRE, OR RIBBON CABLE.
CONDUCTOR TYPE AND LENGTH MUST BE SPECIFIED IN NANONICS PART NUMBER.
- 4

THIS DRAWING PREVIOUSLY IDENTIFIED AS NANONICS 303-0010-XX

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

C. SCHOLL

14 APR 04

CHK

M. STORRY

14 APR 04

APVD

—

—

PRODUCT SPEC

—

—

APPLICATION SPEC

—

—

WEIGHT

—

—

CUSTOMER DRAWING

SCALE

6:1

SHEET

1 OF 1

REV

B

Tyco
Electronics

Tyco Electronics Corporation
Harrisburg, PA 17105-3608

NAME

RECEPTACLE ASSEMBLY, PANEL MOUNT,
SINGLE ROW DUALLOBE, FLYING LEAD,
METAL SHELL

SIZE

A2

CAGE CODE

0PJN9

DRAWING NO

C=1589851

RESTRICTED TO

—

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1589851-4](#)