

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT



By

ALL RIGHTS RESERVED

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A3	REVISED PER ECR-16-014661	26OCT2016	JH	TIME

- 1 SPECIFICATION: WIRE RANGE; #18-#34 AWG.
0.16-1.02 DIA [.006-.040] mm. COPPER MAGNET WIRE.
- 2 POCKET RECOMMENDATION: 1601424.
- 3 TERMINAL APPLICATION TO COMPLY WITH TYCO ELECTRONICS
SPECIFICATION 114-13166. CONSULT PRODUCT ENGINEERING
FOR PROPER INSERTION DEPTH.
- 4 POST PLATED 2 - 3.8 MICRONS TIN OVER 2.5 MICRONS
MIN COPPER.
- 5 THIS LENGTH IS SELECTIVELY POST PLATED WITH 2-3.8 MICRONS
SILVER OVER 1.25 MICRONS MIN NICKEL. SILVER MAY EXTEND
ONTO CARRIER. BALANCE OF TERMINAL IS NICKEL PLATED ONLY.
- 6 PRELIMINARY - NOT FOR PRODUCTION.



	2-1601203-3
	2-1601203-2
	 1601203-2
FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.						DWG M.S. FEHER	050CJ2004		
DIMENSIONS: mm [INCHES] 						TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHEK G. JACONO	050CJ2004	 TE Connectivity
						APPROV G. JACONO	050CJ2004	NAME	
STANDARD RANGE WIRE TO .187 [4.75] X .020 [0.51], OFFSET TAB SAMEZE TERMINAL						PRODUCT SPEC			
APPLICATION SPEC						108-2085			
WEIGHT						3			
MATERIAL	FULL HARD BRASS	SEE TABLE	FINISH			SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
						A1	00779	C1601203	-
CUSTOMER DRAWING						SCALE		SHEET	REV
						11:1		1 OF 1	A3

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-1601203-3](#)