

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B2	REVISED PER ECO-11-005150	29MAR2011	RK	HMR
	W	ECR-16-003733	12MAR2016	KR	TN

LASER MARKING: TE LOGO PN VALUE
TOLERANCE & DATE CODE

M6 ST/STEEL TERMINAL STUDS.
EACH SUPPLIED WITH:-
2 OFF M6 ST/STEEL FULL NUTS
2 OFF M6/STEEL PLAN WASHERS


5.6 MIN

6 HOLES Ø5.3


- 1 FOR FURTHER INFORMATION SEE DATA SHEET FOR
HS SERIES-ALUMINIUM HOUSED RESISTORS
- 2 FOR A SPECIFIC PN FOR A RESISTANCE VALUE
AND TOLERANCE, PLEASE REFER TO DMF

HSC200
ALUMINIUM HOUSED
POWER RESISTOR


RoHS Compliant




SCALE 1:2



GOLD ANODISED
ALUMINIUM HOUSINGS



THIS DRAWING IS A CONTROLLED DOCUMENT.			DWN L LUONG 10.MAR.03		TE Connectivity										
			CHK J CATCHPOLE 10.MAR.03												
			APVD J CATCHPOLE 10.MAR.03												
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME HSC200 ALUMINIUM HOUSED POWER RESISTOR											
		0 PLC ±0.5		APPLICATION SPEC - - - - - WEIGHT -											
		1 PLC ±0.2													
		2 PLC ±0.1													
		3 PLC ±													
		4 PLC ±													
ANGLES ±5°															
MATERIAL - material_2		FINISH - finish_spec_2		SIZE A3				CAGE CODE 00779		DRAWING NO C-1630019		RESTRICTED TO -			
CUSTOMER DRAWING										SCALE 1:1		SHEET 1 OF 1		REV W	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[HSC2002K4J](#)