

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B2	REVISED PER ECO-11-005150	29MAR2011	RK	HMR
	W	ECR-16-003733	12MAR2016	KR	TN

LASER MARKING: TE LOGO PN VALUE
TOLERANCE & DATE CODE

M6 ST/STEEL TERMINAL STUDS.
EACH SUPPLIED WITH:-
2 OFF M6 ST/STEEL FULL NUTS
2 OFF M6/STEEL PLAN WASHERS


5.6 MIN

6 HOLES Ø5.3


- 1 FOR FURTHER INFORMATION SEE DATA SHEET FOR
HS SERIES-ALUMINIUM HOUSED RESISTORS
- 2 FOR A SPECIFIC PN FOR A RESISTANCE VALUE
AND TOLERANCE, PLEASE REFER TO DMF

HSC200
ALUMINIUM HOUSED
POWER RESISTOR


RoHS Compliant




SCALE 1:2



GOLD ANODISED
ALUMINIUM HOUSINGS



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L LUONG	10.MAR.03	 TE Connectivity	
		CHK J CATCHPOLE	10.MAR.03		
		APVD J CATCHPOLE	10.MAR.03		
		PRODUCT SPEC			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME HSC200 ALUMINIUM HOUSED POWER RESISTOR	
		0 PLC	±0.5	SIZE A3	
		1 PLC	±0.2		
		2 PLC	±0.1		
		3 PLC	±		
		4 PLC	±		
		ANGLES	±5°	CAGE CODE 00779	
MATERIAL -		FINISH -		DRAWING NO C-1630019	
material_2		finish_spec_2		RESTRICTED TO -	
CUSTOMER DRAWING			SCALE 1:1	SHEET 1 OF 1	REV W

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[HSC20010RJ](#)