



Wire Protection & Management > Heat Shrink Molded Shapes > Heat Shrink Boots > Bulbous Heat Shrink Boots: Lipped, Straight



Molded Part Angle: 180 °  
Molded Part Shape Code: 202  
Lipped: Yes  
Material Code: 25  
Heat Shrink Boot Material Systems Code: 25

[All Bulbous Heat Shrink Boots: Lipped, Straight \(487\)](#)

Features

Product Type Features

|                   |       |
|-------------------|-------|
| Molded Part Angle | 180 ° |
|-------------------|-------|

Configuration Features

|        |     |
|--------|-----|
| Lipped | Yes |
|--------|-----|

Body Features

|                                        |                                    |
|----------------------------------------|------------------------------------|
| Material Code                          | 25                                 |
| Heat Shrink Boot Material Systems Code | 25                                 |
| Adhesive Pre-Coat                      | Yes                                |
| Material                               | Fluid Resistant Modified Elastomer |

Dimensions

|                             |                  |
|-----------------------------|------------------|
| Inside Diameter as Supplied | 28.4 mm[1.12 in] |
|-----------------------------|------------------|

Usage Conditions

|                             |                             |
|-----------------------------|-----------------------------|
| Operating Temperature Range | -75 – 150 °C[-103 – 302 °F] |
|-----------------------------|-----------------------------|

Operation/Application

|                       |    |
|-----------------------|----|
| Power Cable Accessory | No |
|-----------------------|----|

Industry Standards

|                    |                           |
|--------------------|---------------------------|
| Approved Standards | VG95343 Parts 6,7,8 and 9 |
|--------------------|---------------------------|



|                             |                                               |
|-----------------------------|-----------------------------------------------|
| Government Qualified        | No                                            |
| Other                       |                                               |
| Molded Part Shape Code      | 202                                           |
| Fluid & Chemical Resistance | Long-Term Fluid Exposure at High Temperatures |
| Adhesive Options            | /42 Precoat                                   |
| Adhesive Type               | General Purpose Pre-Coat Adhesive             |

Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                                                                                                               |
|-----------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                     |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                     |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                       |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JUL 2021 (219)<br>Candidate List Declared Against: JUL 2021 (219)<br>Does not contain REACH SVHC |
| Halogen Content                               | Not Low Halogen - contains Br or Cl > 900 ppm.                                                                                |
| Solder Process Capability                     | Not applicable for solder process capability                                                                                  |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CJ2087-000  
[HL2010E-KIT-120V](#)

Customers Also Bought




TE Part #5039264026  
[DR-25-3/8-0-SP](#)



TE Part #EG8288-000  
[202D221-4-61/42-0-CS5503](#)




TE Part #YDTS24T17-08SBV001  
[RECP ASSY](#)



TE Part #1490584-1  
[EXTRACTION TOOL,AMPMODU](#)



TE Part #2837261-1  
[OCEAN\\_2.0\\_Applicator-S-055F0600](#)



TE Part #096281-000  
[55PC6123-24-9-9](#)



TE Part #680112-000  
[D-150-22](#)



TE Part #YAFD56-8-33SWC0190  
[PLUG ASSY](#)



TE Part #ZPF100000000007721  
[983-0SE 24-30 SN-L](#)

Documents

Product Drawings

[202D132-25/42-0](#)

English

Datasheets & Catalog Pages

[1654025\\_Sec4\\_-25](#)

English

[Raychem Molded Parts Visual Guide](#)

English



Product Specifications

Product Specification

English

Product Environmental Compliance

Safety Datasheet

Safety Datasheet

English

Safety Datasheet

French

Safety Datasheet

German

Safety Datasheet

Safety Datasheet

Safety Datasheet

Safety Datasheet

Safety Datasheet

Safety Datasheet

English

Safety Datasheet

French

Safety Datasheet

German

Safety Datasheet

Safety Datasheet

Safety Datasheet

Safety Datasheet

Safety Datasheet

English

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[202D132-25/42-0](#)