






W/O LED LIGHT




RECOMMENDED PCB LAYOUT (THICKNESS: 1.6mm)
(DIMENSION TOLERANCE: 1 PLC: ± 0.1 2PLC: ± 0.05)

△6. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI






OBSOLETE	REEL	W/O	50μ"	3-1734719
			30μ"	3-1734719
			15μ"	3-1734719
			6μ"	3-1734719
		W/	50μ"	3-1734719
			30μ"	3-1734719
			15μ"	3-1734719
			6μ"	3-1734719
6 OBSOLETE	TRAY	W/O	50μ"	1734719-8
			30μ"	1734719-7
			15μ"	1734719-6
			6μ"	1734719-5
OBSOLETE	6 OBSOLETE OBSOLETE OBSOLETE	W/	50μ"	1734719-4
30μ"			1734719-3	
15μ"			1734719-2	
6μ"			1734719-1	
	PACKAGE	LED LIGHT	MIN. GOLD THICKNESS	PART NUMBER

A300779		C-1734719		—	
		SCALE	—	SHEET	1 OF 4
				REV	A2




DETAIL W

TE LOGO &
DATE CODE



RECOMMENDED PCB LAYOUT (THICKNESS: 1.6mm)
(DIMENSION TOLERANCE: 1 PLC: ±0.1 2PLC: ±0.05)



W/O LED LIGHT

NOTE:

- MATERIAL:
HOUSING: THERMOPLASTIC HIGH TEMP., UL94V-0, COLOR: BLACK.
CONTACT: PHOSPHOR BRONZE, THICKNESS: 0.35mm.
SHELL: BRASS, THICKNESS: 0.20mm.
- FINISH:
CONTACT: GOLD PLATED (SEE TABLE) IN CONTACT AREA,
GOLD FLASH ON SOLDER TAILS,
50u" MIN. NICKEL UNDER PLATED ALL OVER.
SHELL: 20u" MIN. NICKEL PLATED.
- WAVE SOLDER CAPABLE TO 265°C PER TYCO SPEC 109-202,
CONDITION B.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	—	TE Connectivity			
		CHK	—				
		APVD	—	NAME			
		PRODUCT SPEC	—				
		APPLICATION SPEC	—	MODULAR JACK, RJ45, SINGLE ENTRY, DIP TYPE			
		WEIGHT	—				
DIMENSIONS: MM		TOLERANCES UNLESS OTHERWISE SPECIFIED:		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
				A3	00779	C=1734719	—
				CUSTOMER DRAWING			
				SCALE	—	SHEET	2 of 4
						REV	A2

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

-,-



COPYRIGHT 2013

BY TE CONNECTIVITY.

ALL RIGHTS RESERVED.

LOC
DWDIST
—

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1

TOP TRAY

CLAPBOARD

INNER BOX

BOX

370mm(L)X255mm(W)X220mm(H)
11 TRAY/CARTON
TOTAL: 880 PCS
GROSS WEIGHT: 5Kg Ref.

TRAY

330mm(L)X225mm(W)X15mm(H)
80 PCS/TRAY

H

W

L

W

L

H

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

—

CHK

—

APVD

—

PRODUCT SPEC

—

APPLICATION SPEC

—

WEIGHT

—

CUSTOMER DRAWING

DIMENSIONS:

MM



MATERIAL

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±

FINISH



TE Connectivity

NAME

MODULAR JACK, RJ45, SINGLE
ENTRY, DIP TYPE

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C=1734719

—

SCALE

—

SHEET

3 of 4

REV A2

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

-,-

© COPYRIGHT 2013 BY TE CONNECTIVITY.

ALL RIGHTS RESERVED.

LOC
DWDIST
—

REVISIONS

P

LTR





DESCRIPTION

DATE

DWN

APVD

SEE SHEET 1



NOTES:

- THE DIRECTION OF JACKS PUT INTO CARRIER.
- 10 EMPTY CAVITIES FOR BOTH OF TOP AND BOTTOM OF THE CARRIER.
- 200 PCS PRODUCTS BE PACKAGED ONE REEL.
- BOX SIZE: 345(L)X345(W)X315(H)
6 REEL/BOX
TOTAL: 1200 PCS

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

MM

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±

MATERIAL

FINISH

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

NAME

SIZE

A3

CAGE CODE

00779

DRAWING NO

C=1734719

RESTRICTED TO

—

SCALE

—

SHEET

4 of 4

REV

A2

TE

TE Connectivity

MODULAR JACK, RJ45, SINGLE ENTRY, DIP TYPE

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1734719-2](#)