





LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
CM	00		C1	REVISED PER ECO-11-014117	11JUL11	HMR SM



RECOMMENDED MOUNTING HOLE PATTERN
FOR 1.60 [.063] THICK P.C. BOARD

- 1 POST TO WITHSTAND 13 NEWTONS (3LBS.) MIN. AXIAL FORCE IN BOTH DIRECTIONS SHOWN WITHOUT DISLODGING.
- 2 TOLERANCES APPLY TO SOLDER SIDE OF BOARD.
- 3 MEASURED AT SURFACE -A- .
- 4 PLASTIC FLASH PERMITTED IN THIS AREA.
- 5 PARTS COMPLY WITH AMP SOLDERABILITY SPEC. NO. 109-11-2.
- 6 ONE HOLE MAY BE UNDERSIZED 1.65 [.065]-1.52 [.060] ASSEMBLY RETENTION DURING WAVE SOLDERING.
- 7 MATERIAL: HEADER-THERMOPLASTIC POLYESTER
GLASS-FILLED 94V-0 (NATURAL)
POST-COPPER ALLOY (TIN OR TIN-LEAD PLATED
-SEE TABLE FOR DETAILS).
- 8 COORDINATE DIMENSION APPLIES FROM CENTER OF ACTUAL FEATURE.
- 9 PLASTIC BURRS CAUSED BY CUT-OFF TOOLING ARE PERMITTED WITHIN THE MAXIMUM TOLERANCE ENVELOPE.
- 10 POST TO BE MEASURED WHEN STRIP IS HELD FLAT.
- 11 POST MUST WITHSTAND TWO 90° BENDS AGAINST EXTRUSION WITHOUT BREAKING.
- 12 DIMENSION SHOULD BE 4.45 [.175] MIN WHEN MATING WITH A MTA .156 CONNECTOR ASSEMBLY OR A SL-.156 CONNECTOR ASSEMBLY.
- 13 MAXIMUM PIN BURR OF 1.65 [.005] HIGH X 1.52 [.003] WIDE PERMITTED AT POST TIPS ON BOTH ENDS.

OBSOLETE	TIN	3-1744046-1
	TIN-LEAD	1744046-1
	FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. WHITAKER 31MAR04	 TE Connectivity								
DIMENSIONS: mm [INCHES]		CHK D. BOSSI 31MAR04									
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D. BOSSI 31MAR04	NAME	MTA-.156 HEADER ASSEMBLY, FRICTION LOCK, STRAIGHT .045 SQUARE POST, TIN LEAD PLATED, 4 POSITION, SPECIAL							
		PRODUCT SPEC		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO				
		APPLICATION SPEC									
		WEIGHT						A1	00779		1744046
		CUSTOMER DRAWING									
		SCALE									

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1744046-1](#)