

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
FT	0		02	REVISED PER ECO-12-007711	26APR2012	KH	MS

D

C

B



A

D




C

B

A



- ⚠ MATERIALS AND FINISH
HOUSING: HIGH TEMPERATURE POLYAMIDE, UL 94V-0 RATED,
COLOR: BLACK.
TERMINAL: COPPER ALLOY, TIN PLATED.
2. SUITABLE FOR 1,6-2,4mm PC BOARD THICKNESS.
3. END-TO-END STACKABLE WITHOUT LOSS OF CENTERLINE SPACING.
4. RECOGNIZED UNDER THE COMPONENT PROGRAM OF UNDERWRITERS LABORATORIES INC.FILE N° E60677.
5. IMQ CERTIFICATE WITH SURVEILLANCE IN CONFORMITY WITH IEC 998-1/998-2-1.
6. UL RATING: 300V, 15A.



RECOMMENDED PC BOARD LAYOUT

60.48±0.20	12	1-1776141-2
55.40±0.20	11	1-1776141-1
50.32±0.20	10	1-1776141-0
45.24±0.15	9	1776141-9
40.16±0.15	8	1776141-8
35.08±0.15	7	1776141-7
30.00±0.15	6	1776141-6
24.92±0.10	5	1776141-5
19.84±0.10	4	1776141-4
14.76±0.10	3	1776141-3
9.68±0.10	2	1776141-2
A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. WELDON 07JUN2005	 TE Connectivity			
DIMENSIONS:		CHK C. RICHARD 07JUN2005				
mm		APVD C. RICHARD 07JUN2005	NAME TERMINAL BLOCK HEADER ASSEMBLY 90 DEGREE, OPEN ENDS, STACKING 5.08mm PITCH			
		PRODUCT SPEC 108-20166	SIZE A2		CAGE CODE 00779	DRAWING NO C-1776141
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC 114-20079	RESTRICTED TO		-	
0 PLC ±.2 1 PLC ±.25 2 PLC ±.25 3 PLC ±. 4 PLC ±. ANGLES ±2 FINISH		WEIGHT -	SCALE 3:1		SHEET 1 OF 1	REV 02
MATERIAL		CUSTOMER DRAWING				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1776141-7](#)