



Application Tooling > Portable Crimp Tools



Power Technology Type: **Hydraulic (10,000 psi)**
Tooling Type: **Base Power Unit (No Crimp Tooling)**

Features

Other

Power Technology Type	Hydraulic (10,000 psi)
Tooling Type	Base Power Unit (No Crimp Tooling)

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2021 (219) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability













Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides






on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # 321259-1 TERM, SOLIS FLAG HR 4/0 1/2</p>	 <p>TE Part # 324657 SPLICE BUTT M-M TERMINYL 8</p>	 <p>TE Part # 2-329491-2 SPLICE,TERMI-FOIL 12 IN.</p>	 <p>TE Part # 165429-1 SHUR PLUG REC.ASSY</p>
 <p>TE Part # 1SET164006R0000 SPR025-N</p>	 <p>TE Part # 2-329490-2 SPLICE,TERMI-FOIL 12 IN.</p>	 <p>TE Part # 2-329491-3 SPLICE,TERMI-FOIL 15 IN.</p>	 <p>TE Part # 321866-1 STRATO-THERM, HR 1/0 1/4 NIPL</p>
 <p>TE Part # 321874-2 STRATO-THERM, HR 3/0 5/16 NIPL</p>	 <p>TE Part # 321875-1 STRATO-THERM, HR 3/0 3/8 NIPL</p>	 <p>TE Part # 321880-1 STRATO-THERM, HR 4/0 1/2 NIPL</p>	 <p>TE Part # 696434-1 TERM, RING, PLASTI-GRIP, 4, #10, 90 BEND</p>

Customers Also Bought

 <p>TE Part #525449-4 SLIP GAUGE, HANDTOOL</p>	 <p>TE Part #525449-5 SLIP GAUGE, HANDTOOL</p>	 <p>TE Part #1-532433-2 HDI PIN ASSY 3 ROW 225 POS</p>	 <p>TE Part #2102573-1 ASSY 2/0 AL COPALUM LITE SINGLE HOLE 3/8</p>
---	---	---	--





TE Part #2-1618071-2
25-060-4X=WILMAR OVER/UNDERFRE



TE Part #293247-000
2522D0522-9



TE Part #290578-001
44A7422-0-1L



TE Part #766667-2
Wave Crimp, Flat to Round 8 AWG
Cbl Assy



TE Part #1616109-3
A700AP=RELAY



TE Part #CTJ-3A-02-4032
RAIL ASSY

Documents

Datasheets & Catalog Pages

[AT-Hydraulic Crimp Tooling Solutions-1654519](#)

English

[Crimp Term Whitepaper-Use the Right Tool 1-1773953-1](#)

English

[CRIMPING WHERE FORM MEETS FUNCTION](#)

English

[Bottoming Dies](#)

English

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1583661-1](#)