



Connectors > D-Shaped Connectors > D-Sub Accessories > Locking & Mounting



D-Shaped Connector Accessories: **Female Screwlocks**

Screw Length: 12.7 mm [.5 in]

Features

Product Type Features

Product Type	Accessory
D-Shaped Connector Accessories	Female Screwlocks

Mechanical Attachment

Screwlock Style	Screwlock Only
Mating Thread Size	M3
Screw Finish	None
Screw & Hole Thread Size	4-40 UNC 2B (Female), M3 (Male)
Screw Length	12.7 mm[.5 in]

Dimensions

Thread Length	7.92 mm[.312 in]
---------------	------------------

Packaging Features

Packaging Quantity	1000
Packaging Method	Bag

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Yet Reviewed
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2021 (219)



Candidate List Declared Against: JUN 2012 (84)
SVHC > Threshold:
Not Yet Reviewed

Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # 829261-6
HD FEMALE SCREWLOCK



TE Part # 176152-3
SCREWLOCK KIT FOR AMPLIMITE

Also in the Series | **AMPLIMITE Kit**



D-Sub Backshells & Clamps(136)



D-Sub Contact Accessories(1)



D-Sub Covers(3)



D-Sub Locking & Mounting(122)

Customers Also Bought



TE Part #5745784-4
37 MSFL RCPT RA 318 (IN,FM)

TE Part #5228226-3
BNC BLKHD JACK ADAPTER GOLD

TE Part #51494-2
STD HIGH VOLTAGE BLKHD RECEPT

TE Part #1054868-1
2084 0000 00

TE Part #5-146280-1
01 MODII HDR SRST B/A LF

TE Part #31423
TERMINAL,BUDG R 26-22, 0

TE Part #51426-2
SAFE HIGH VOLTAGE PLUG

TE Part #227755-1
BNC SOLDER RECEPT JACK SHORT

TE Part #221551-3
FEEDTHRU,JACK,BNC,REPACKAGE

TE Part #D54859-000
VERSAFIT-KIT-2-COLOR

Documents

Product Drawings
AMPLIMITE SCREWLOCK M3

Japanese

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_174888-1_A.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_174888-1_A.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_174888-1_A.3d_stp.zip
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications



Application Specification

English

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[174888-1](#)