



Application Tooling > Portable Crimp Tools



Tool Grade: **Premium Crimp Tooling**
Die Sets Type: **Removable/Interchangeable**
Specification Type: **MIL Spec, TE Product Specification (114-)**
TE Certification: **Cannot be Certified**
Power Technology Type: **Battery, Hydraulic, Manual**

Features

Other

Crimp Form-Wire Barrel Type	Closed Barrel - W Crimp
Tool Grade	Premium Crimp Tooling
Die Sets Type	Removable/Interchangeable
Specification Type	MIL Spec, TE Product Specification (114-)
TE Certification	Cannot be Certified
Power Technology Type	Battery, Hydraulic, Manual
Tooling Type	Die Assembly

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUL 2021 (219) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content




Solder Process Capability

Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




TE Part # 322727
TERMINAL,SOLIS FLAG R 8 1/4



TE Part # 321051
TERMINAL,SOLIS FLAG R 8 10



TE Part # 321441
TERMINAL,SOLIS FLAG R 8 10



TE Part # 696722-1
STRATO-THERM, FLAG R 8 8 NIPL



TE Part # 1490749-1
HYP10 8-4/0AWG MANUAL TOOL



TE Part # 696611-1
SOLISTRAND 8 FLAG #6 STUD




TE Part # 1490746-1
HYP10 LIGHT DUTY 14T HEAD

Customers Also Bought



TE Part #1217378-3
RAST 5 POSI LOCK MKIII,22-18 A



TE Part #1285002-2
PROCRIPTER TOOL & DIE



TE Part #1752680-7
HYP10 SOLIS FLAG 6AWG NEST



TE Part #1752681-2
HYP10 SOLIS FLAG 8AWG INDENTER



TE Part #2266174-2
OCEAN-2.0-APPLICATOR-S-070F1000

TE Part #ZPF000000000007238
983-ORS 18-02 P6 L-A1325

TE Part #YACT24JB99PNV00100
JAM NUT RECEPTACLE

TE Part #ZPF400000000007238
983-ORS 18-02 P6 L-A1325

Documents

Datasheets & Catalog Pages

[AT-Hydraulic Crimp Tooling Solutions-1654519](#)

English

[Crimp Term Whitepaper-Use the Right Tool 1-1773953-1](#)

English

[CRIMPING WHERE FORM MEETS FUNCTION](#)

English

[Bottoming Dies](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1752680-8](#)