




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
E	B		BB	ECR-15-016499	16NOV2015	KR	TN

NOTES:

1. POWER RATING: 200W
2. INSULATION RESISTANCE: DC 500V - 20 M Ohms Min
3. VOLTAGE RESISTABILITY: AC 2500V 1 MINUTE
4. UP TO 9R1 RIBBED 10R UPWARD SMOOTH.
5. TUBE BORE AND SIDE FACES SHOULD BE FREE OF PAINT
6. PARTS SHALL BE BLANK, SMOOTH, FREE OF BURRS AND ALL OTHER FOREIGN MATERIAL
7. FOR FURTHER INFORMATION SEE DATASHEET FOR TE SERIES HIGH POWER WIRE WOUND RESISTOR
8. FOR SPECIFIC PART NUMBER, RESISTANCE VALUE AND TOLERANCE PLEASE REFER TO SMART PART SEARCH



RoHS Compliant

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN PRASAD K 26SEP2011	 TE Connectivity				
DIMENSIONS: mm		CHK J.CATCHPOLE 26SEP2011					
		APVD J.CATCHPOLE 26SEP2011	NAME HIGH POWER WIRE WOUND RESISTOR TE 200W SERIES				
		PRODUCT SPEC					
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC	SIZE		CAGE CODE	DRAWING NO	RESTRICTED TO
0 PLC ±0.5 1 PLC ±0.1 2 PLC ±0.05 3 PLC ± 4 PLC ± ANGLES ±0.5° FINISH		-	-		-	-	-
MATERIAL		WEIGHT	A2 00779		C=1879447		-
-		-	Customer Drawing				SCALE 1:1 SHEET 1 OF 1 REV BB

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[4-1879447-0](#)