

4

3



2

1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION OCT, 2001.


© COPYRIGHT 2001 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
ES			A1	ECR-10-014987	19JUL10	B.W S.Y






HOW TO MATE AND UNMATE

MATE: ① → ④
UNMATE: ⑤ → ⑦




(APPLIED TO SHEET 1-2)

1. MATERIAL ; HOUSING: HIGH TEMPERATURE THERMO PLASTIC UL94V-0
CONTACT: COPPER ARROY
LOCK LEVER STAINLESS STEEL
SOLDER PEG: COPPER ARROY
- △ FINISH ; CONTACT AREA: GOLD FLASH ON 0.0013MIN ALL OVER NICKEL.
SOLDERING AREA: GOLD FLASH PLT.
SOLDER PEG: TIN PLATING.
- △ MECHANICAL KEY POSITION OF CONNECTOR SEE TABLE.
- △ TOLERANCES NON-CUMULATIVE.
- △ NOT TO SCALE.
- △ [] INSIDE MUST BE RESIST COAT EXCEPT SOLDER PATTERN.
7. IF THE MODULE DOESN'T INSERT AND LOCK IN THE LATCH SMOOTHLY,
OPEN WIDE BOTH LATCHES BY MANUAL. AND THE MODULE MUST BE
INSERTED AND LOCKED IN THE LATCH.




GENERAL TOLERANCE
10 $\geq$: $\pm$ 0.2
30 $\geq$ >10: $\pm$ 0.25
100 $\geq$ >30: $\pm$ 0.3
ANGLES: $\pm$ 3°


△	—	1.8V (DDR2)	17.55	2.4	2.7	200	1932179-1
PLATING	TOOLING STATUS	POWER SUPPLY	D5	D4	D3	POS	PART NO.
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.KEVIN 24SEP08	 Tyco Electronics Corporation Shanghai, P.R.China, 200233				
		CHK T.FUMIKURA 26SEP08					
DIMENSIONS: MM		APVD Y.STEVEN 27SEP08	NAME				
		PRODUCT SPEC	DDR2 SODIMM SOCKET 0.6mm PITCH 200POS				
		APPLICATION SPEC	STANDARD PROFILE STANDARD TYPE (NEW PEG TYPE)				
MATERIAL		WEIGHT	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
		—	A3	00779	C-1932179	—	
CUSTOMER DRAWING						SCALE 2:1	SHEET 1 OF 4 REV A1

LOC ES	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			—	SEE SHEET 1	—	—	—

REFERENCE P.C.BOARD PATTERN LAYOUT
(CONNECTOR MOUNTING SIDE)



REAL SIZE (SCALE 1:1)



1.8V	17.55	2.4	2.7
POWER SUPPLY	D5	D4	D3

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
MM

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±

1 PLC ±

2 PLC ±

3 PLC ±

4 PLC ±

ANGLES ±

FINISH ±

MATERIAL

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

Tyco Electronics Corporation
Shanghai,P.R.China,200233

NAME

DDR2 SODIMM SOCKET
0.6mm PITCH 200POS
STANDARD PROFILE STANDARD TYPE (NEW PEG TYPE)

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-1932179

—

SCALE

2:1

SHEET

2 OF 4

REV

A1

AMP 1470-19 REV 31MAR2000


4

3

2

1

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	APVD
ES			—	SEE SHEET 1	—	—



(APPLIED TO SHEET 4)

1 THE DIRECTION OF EACH CONNECTOR ON A TRAY IS REFERRED TO THIS DRAWING.

2 GENERAL TOLERANCE: ± 0.5

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
MM

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC $\pm$

1 PLC $\pm$

2 PLC $\pm$

3 PLC $\pm$

4 PLC $\pm$

ANGLES $\pm$

FINISH

MATERIAL

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

Tyco Electronics Corporation
Shanghai,P.R.China,200233

NAME
DDR2 SODIMM SOCKET
0.6mm PITCH 200POS
STANDARD PROFILE STANDARD TYPE (NEW PEG TYPE)

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-1932179

RESTRICTED TO
—

SCALE 1:2

SHEET 4 OF 4

REV A1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1932179-1](#)