




4



3

2




1


LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
ES	—		—	SEE SHEET 1	—	—	—

REFERENCE MATING P.C.B CONFIGURATION



- (APPLIED TO SHEET 3)
1. TOLERANCES ON ALL DIMENSIONS ±0.15 UNLESS OTHERWISE SPECIFIED.
 2. P.C. BOARD THICKNESS APPLIES ACROSS TABS AND INCLUDES PLATING AND/OR METALIZATION.
 3. FINISH OF PAD : GOLD PLATING 0.00076 MIN. OVER Ni PLATING 0.002MIN.
- NO BURR
CHAMFER 0.25 MAX x 45° IF EXIST.



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	 TE Connectivity			
		CHK				
DIMENSIONS: MM	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD	NAME			
	0 PLC ±	PRODUCT SPEC	DDR3 SODIMM SOCKET			
	1 PLC ±		0.6mm PITCH 204POS			
	2 PLC ±		5.2mm HEIGHT STANDARD TYPE			
	3 PLC ±	APPLICATION SPEC	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
	4 PLC ±		A3	00779	C-1932207	—
	ANGLES ±	WEIGHT				
MATERIAL	FINISH	CUSTOMER DRAWING				
		SCALE	2:1	SHEET	3 OF 4	REV C

4




3

2



1

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	APVD
ES			-	SEE SHEET 1	-	-

DIRECTION OFF TOP OF REEL →



- (APPLIED TO SHEET 4)
1. THE DIRECTION OF EACH CONNECTOR ON A EMBOSS IS REFERRED TO THIS DRAWING.
 2. GENERAL TOLERANCE: ± 0.5 , $\pm 3^\circ$



FREE SCALE

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
MM

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± 0.5
1 PLC ± 0.5
2 PLC ± 0.5
3 PLC ± 0.5
4 PLC ± 0.5
ANGLES ± 3°
FINISH

DWN
CHK
APVD
PRODUCT SPEC
APPLICATION SPEC
WEIGHT

TE Connectivity

NAME
DDR3 SODIMM SOCKET
0.6mm PITCH 204POS
5.2mm HEIGHT STANDARD TYPE

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-1932207

RESTRICTED TO
-

CUSTOMER DRAWING

SCALE
1:2

SHEET
4 OF 4

REV
C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1932207-2](#)